



## R112ML0650LSG

**Straight Section for WR112, 7.05–10.0 GHz, with interface types UDR84 and UDR84, 650 mm, gray**

### Electrical Specifications

|                          |                 |
|--------------------------|-----------------|
| Operating Frequency Band | 7.05 – 10.0 GHz |
| VSWR                     | 1.05            |

### General Specifications

|                |                    |
|----------------|--------------------|
| Component      | Straight Section   |
| Waveguide Size | WR112   WG15   R84 |
| Finish         | Gray               |
| Interface      | UDR84              |
| Interface 2    | UDR84              |
| Length         | 650 mm   26 in     |

### Component Interface Interface 2



### Regulatory Compliance/Certifications

|               |                                                                                |
|---------------|--------------------------------------------------------------------------------|
| <b>Agency</b> | <b>Classification</b>                                                          |
| ISO 9001:2008 | Designed, manufactured and/or distributed under this quality management system |