

960H Digital Video Recorder **DW-VC 4**



Summary

The VMAX960H CORE $^{\text{TM}}$ is an advanced H.264 embedded digital video recorder that records real-time at 960H Resolution. This DVR offers the unparalleled image quality of the VMAX960H, at an affordable cost for small and mid-size applications. In addition, the DVR offers great features such as Free DDNS, One Touch Backup and Playback, True DVR Health Check with E-mail Notifications and is supported by our popular mobile application. The VMAX960H CORE $^{\text{TM}}$ is available with up to 4 Terabytes of storage.

Features


- 34% MORE Resolution with True 960x480 Display Recording
- Pivot™ Central Management Software, Up to 128CH
- Mobile Application for iPhone, iPad, iPod, Android Smart Phones and Tablets, and Kindle Fire
- · MAC Compatible Remote ACS Software
- · Intuitive Graphical User Interface (GUI)
- HDD Calculation and Auto Recording Configuration
- Event Notifications via Email. Text and Pivot™ CMS
- Advanced H.264 Embedded DVR
- Multiplex Live, Playback, Recording, Backup, Network, Configuration
- · Record 30 Frames per Second on Every Channel
- 1 Audio Input, 1 Audio Output
- · 4 Sensor Input, 1 Relay Output
- Simple & Free DDNS Service
- Easy Web-Based Client with Multi-User Access
- Scheduled Network Backup
- Watermark Verification (Digital Signature Verification)
- Help Menu on Major Functions
- · Auto & Manual Firmware Upgrade Available
- Import/Export Configuration Between Multiple DVRs
- USB Mouse, IR Remote Control, GUI

Available Models

- DW-VC 161T
- DW-VC 162T
- DW-VC 163T
- DW-VC 164T

Dimensions (unit: mm)





Specifications

VIDEO		4 Channels
Video Input	F D.	4 Channels
Video Live	Frame Rate	1~30fps
	Resolution	960x480, 960x240, 480x240
Video Output		HD Output, Composite, SPOT
Audio	Input	1 Input (Via Phone Jack)
	Output	1 Output (Via Phone Jack)
	Audio Codec	PCM
Alarm	Sensor Input	4 Input
	Alarm Out	1 Output
Operating System		Embedded Linux
Serial		2xRS485 for PTZ Camera & Controller, 2xUSB 2.0
User Interface	Menu Display	Graphical User Interface (GUI)
	Control Methods	IR Remote Control, USB Mouse
Screen Display Mode		1, 4, Sequence
Screen Resolution		1920x1080P, 1280x1024, 1024x768
PERFORMANC	E	
Recording	Compression	H.264
	Decording Mode	Schedule, Event, Time-Lapse, Panic, Continuous,
	Recording Mode	Pre & Post Event, Motion, Recording Configuration per Channel
	Pre Recording	1~5 Seconds
	Post Recording	5~15 Seconds
	Recording Rate	120fps @ All Resolution (NTSC/PAL)
	Recording Resolutions	Full 960H Real-Time Recording, 30fps @ All Resolutions
Playback	Playback Rate	120fps @ All Resolution (NTSC/PAL)
	Playback Resolution	Full 960H Real-Time Playback, 30fps @ All Resolutions
	Fast Forward Functions	x1/16, x1/8, x1/4, x1/2, x1, x2, x4, x8, x16, x32
		First Data, Last Data, Date/Time, Record Table,
	Playback Functions	Calendar, Bookmark, System Log
Storage	HDD Interface	1 HDD
	Max. Internal HDDs	Up to 4TB (1HDD x 4TB)
	External Storage	USB Flash Drive, USB HDD, DVD
	HDD Interface Type	SATA-II. SATA-III
	HDD Health Check	Temperature, S.M.A.R.T. with E-mail Notifications
Features	Camera Color Control	Brightness, Contrast, Saturation, Hue
	Digital Zoom	Yes (Live & Playback)
	Software Upgrade	USB Flash Drive, Network Upgrade, FTP Remote Upgrade
	Mobile Client	Mobile App for Apple & Android Smart Phones & Tablets
	Covert Channel	Yes (Live & Playback)
	COVERT CHAINE	169 (Live & FidyDdCK)
	on	Ethornot (1 v Monahit 10/100 Mana)
Network Connection Maximum User Connections		Ethernet (1 x Megabit 10/100 Mbps)
waximum user Co		10 Simultaneous Connections
Streaming	Transmission Speed Live	120/100fps @ 960H and CIF (NTSC/PAL)
	Protocols	Static, DDNS, DHCP, uPnP, RTSP
Access	Web Viewer	Live, Playback, & Configuration up to 10 Multiple Connections
	Client Monitoring Software	ACS (Client S/W), MAC (Apple S/W), Pivot (CMS S/W)
GENERAL		
Operating Temperature / Humidity		5 ~ 40°C (41 ~ 104°F)
Operating Humidity		Less than 80% (Non-Condensing)
Electrical	Power Requirement	12V 3.33A D/C
	Power Consumption	30.96W
Dimensions		14.2 x 14.3 x 2.6 inch (360.68 x 363.22 x 66.04mm)
Weight		8.4 lbs (3.8 kg)

 ${}^{\star}\mathsf{Specifications}\,\mathsf{subject}\,\mathsf{to}\,\mathsf{change}\,\mathsf{without}\,\mathsf{notice}.$



866.446.3595 sales@dwcc.tv digital-watchdog.com