



# IS-DM260

## IS-DM260

---

The IS-DM260 is an ultra-compact multi-megapixel security and surveillance network camera. Designed with a discrete form factor, the IS-DM260 is an unobtrusive security and surveillance solution for a variety of applications. A built-in Micro-SD slot allows the IS-DM260-R to be the perfect solution in distributed or standalone surveillance systems.

Launched in July 2010, the IS-DM260-R features full compliance with the ONVIF interoperability standard.

## Dimensions

---

- 4.3 x 1.9 in (110.2 x 47.7 mm)
- 0.40 lb (180 g)

## Performance Specification

---

- Sensor: 2.0MP CMOS
- Maximum Resolution: 1920 x 1080
- Active Pixel Count: 2,073,600
- Maximum Frame Rate: 15 fps (at max res)
- Compression: MJPEG / H.264
- Streaming: Quad H.264 + MJPEG
- 0.1 lux (color) at F/1.5
- Backlight Compensation
- Wide Dynamic Range
- Dynamic Range: 95 dB
- 3D Noise Reduction
- Full Onvif Compatibility

## Technical Specification

---

- Lens: 4 mm fixed
- Mic-In Audio
- Micro-SD Storage
- Motion Detection
- Tamper Detection
- UDP, TCP/IP, HTTP, TFTP, RTP/RTSP
- 100/10 LAN Connection
- Security: Username and password

## Electrical Specification

---

- PoE
- 3.5 watts

## Environmental Specification

---

- Operating Temperature: 14° - 122° F  
-10°C - 50°C
- Humidity: 0% to 90%, No condensation

## Warranty

---

- 3 Year, Parts and Labor

## Images

---



## Dimensional Outline

---

