

# SSP-311-D SPECIFICATIONS


## STAINLESS STEEL AUTODIAL TELEPHONE PANEL WITH HANDSET










Durable stainless steel flush mount panel telephone that will automatically dial a preprogrammed number from 1-11 digits when the handset is lifted off-hook. Equipped with marine quality chrome mechanical hookswitch, ID window or optional (-IVC) pushbutton volume control with background noise reduction, and 32" hearing aid compatible armored cord handset. Telephone can be flush mounted or installed in our 331-005 weatherproof or 331-HOB weather resistant housing.



### SPECIFICATIONS

<b>Panel Size:</b>	7 1/6"W x 11 1/4"H 2"D (Behind Panel) 3"D (Front Panel & Handset on Hook)
<b>Weight:</b>	Approximately 6lbs.
<b>Mounting Instructions:</b>	Flush Mounted Weatherproof Housing (WPP) Weather Resistant Open Enclosure (HOB)
<b>Environment:</b>	Temperature: -30°C (-22°F) to 60°C (140°F) Humidity: 0%-90% non-condensating
<b>Programming:</b>	Via Mini Jumpers
<b>Input Power:</b>	Telephone Line Powered
<b>Loop Current:</b>	23mA min to 80mA max
<b>Impedance:</b>	600 ohms
<b>Type Jack:</b>	RJ11C
<b>Ringer Equivalency:</b>	0.4A
<b>Hearing Aid Compatible:</b>	Meets EIA standards
<b>UL &amp; FCC Registration:</b>	Certified
<b>ACCESSORIES:</b>	301-064 Security Tool (only required for installation when in HOB or WPP)



ADDITIONAL OPTIONS						IP - Voice over Internet Protocol Version available on all models (SIP)		
-M	-IVC	-ACH**	-ACH*	-CCH*	-LB	Open Enclosure Housing	Weatherproof Housing	-RIL
								
Sealed Magnetic Hookswitch • Completely Sealed • No Moving Parts	Internal Volume Control • Push Button Volume Control • Background Noise reduction	Varies armored cord from length 14" to 72"  <b>Example:</b> ACH14: 14" armored cord	Varies handset color  <b>-ACHW</b> White handset  <b>-ACHR</b> Red handset	Coiled cord available from 5', 10', & 15' (feet). Example: <b>-CCH5</b> 5' Long	Handset w/ internal steel lanyard (braided metal rope) and lanyard mounting bracket that is secured onto panel for added strength.	<b>-331-HOB</b> Standard Black Housing <b>-331-HOB-R</b> Red Housing <b>-331-HOB-S</b> Stainless Steel Housing	<b>-331-005</b> Standard Black & TELEPHONE on Door <b>-331-005-EMER</b> Black & EMERGENCY on Door <b>-331-005-R</b> Red & EMERGENCY on Door <b>-331-005-R-TEL</b> Red & TELEPHONE on Door <b>-331-005-Y</b> Yellow & EMERGENCY on Door <b>-331-005-Y-TEL</b> Yellow & Telephone on Door <b>331-005-G</b> Grey & TELEPHONE on Door <b>331-005-G-EMER</b> Grey & EMERGENCY on Door	Ring Indicator Light located on the phone panel for visual ring indication.

Communication Equipment  
& Engineering Company

<http://www.ceeco.net>

Email: [sales@ceeco.net](mailto:sales@ceeco.net)

519 SW Park Street

Okeechobee, FL 34972

Voice 863-357-0798

Fax 863-357-0006