

SSW-323-D SPECIFICATIONS

MINI WALL HANDSET TELEPHONE WITH AUTODIAL & SMART FEATURES


Standard Analog Power, but also available in VoIP versions








Strong and compact small stainless steel surface mount wall telephone that autodial a preprogrammed number when the handset is lifted off-hook. The direct dial or hotline phone is programmable from 1-25 digits, PBX, prefix, or access dialing capability, and incoming call block. Phone is constructed with a marine quality chrome mechanical or magnetic hookswitch, ID window or optional volume control button with background noise reduction, 32" hearing aid compatible armored cord handset with internal steel lanyard and swivel, which is anchored into the housing, tamper resistant security screws, and steel mounting backplate for easy installation. For the toughest environment shorter handset lengths are available in 10, 12, and 18 inch length



SPECIFICATIONS

Panel Size:	5" W x 10.75" H x 3" D 5.5" D With handset on Hook
Weight:	Approximately 7 lbs.
Mounting Instructions:	Vertical Surface Mount: Separate the cover assembly from the backplate. The plate assembly is designed to be mounted on any flat vertical surface. <ul style="list-style-type: none"> 4 holes spaced 3" W x 6" H
Environment:	Temperature: -30°C (-22°F) to 60°C (140°F) Humidity: 0%-90% non-condensing
Input Power:	Telephone Line Powered
Programing:	Via DTMF Keypad
Loop Current:	25mA min to 80mA max
Impedance:	600 ohms
Type Jack:	RJ11C
Ringer Equivalency:	0.4A
Hearing Aid Compatible:	Meets EIA standards
UL& FCC Registration:	Certified
ACCESSORIES:	301-037 Security Tool (required for installation)



ADDITIONAL OPTIONS						
IP - Voice over Internet Protocol Version available on all models (SIP)						
-M	-IVC	-ACH**	-ACH*	-CCH*	-RIL	-RIS
						
Sealed Magnetic Hookswitch • Completely Sealed • No Moving Parts	Push Button Volume Control • Background Noise reducer	Other Length armored cord from 12" to 72"(inches). Example: -ACH12 12" Long	ACHW -White Handset ACHR -Red Handset (Black is standard)	Coiled cord available from 5', 10', & 15' (feet). Example: -CCH5 5' Long	Ring Indicator Light located on the phone panel for visual ring indication	Ring Indicator Flashing Blue Light (Requires AC Power)



Providing Telecommunication Solutions Since 1930

Communication Equipment
& Engineering Company
<http://www.ceeco.net>
Email: sales@ceeco.net

519 SW Park Street
Okeechobee, FL
Voice 863-357-0798
Fax 863-357-0006