

SSW-323-F SPECIFICATIONS

MINI WALL HANDSET TELEPHONE WITH KEYPAD & SMART FEATURES


Standard Analog Power, but also available in VoIP versions

Strong and compact small stainless steel surface mount wall telephone for keypad dialing with call restrictions. Programmable PBX, prefix, or access dialing capability, call time duration setting from no limit up to 30 minutes, allow or block incoming calls, and 40 (1-11 digits) programmable speed dialing locations. Phone is constructed with a marine quality chrome tone dial and mechanical hookswitch, ID window or optional volume control button with background noise reduction, 32" hearing aid compatible armored cord handset with internal steel lanyard and swivel, which is anchored into the housing, tamper resistant security screws, and steel mounting backplate for easy installation. For the toughest environments shorter handset lengths are available in 10, 12, and 18 inch lengths.










SPECIFICATIONS

Panel Size:	5" W x 10.75" H x 3" D 5.5" D With handset on Hook
Weight:	Approximately 7 lbs.
Mounting Instructions:	Vertical Surface Mount: Separate the cover assembly from the backplate. The plate assembly is designed to be mounted on any flat vertical surface. <ul style="list-style-type: none"> • 4 holes spaced 3" W x 6" H
Environment:	Temperature: -30°C (-22°F) to 60°C (140°F) Humidity: 0%-90% non-condensing
Programming:	Via DTMF Keypad
Input Power:	Telephone Line Powered
Loop Current:	25mA min to 80mA max
Impedance:	600 ohms
Type Jack:	RJ11C
Ringer Equivalency:	0.4A
Hearing Aid Compatible:	Meets EIA standards
UL& FCC Registration:	Certified
ACCESSORIES:	301-037 Security Tool (required for installation)



ADDITIONAL OPTIONS

IP - Voice over Internet Protocol Version available on all models (SIP)

-M	-IVC	-ACH**	-ACH*	-CCH*	-RIL	-RIS
						
Sealed Magnetic Hookswitch <ul style="list-style-type: none"> • Completely Sealed • No Moving Parts 	Push Button Volume Control <ul style="list-style-type: none"> • Background Noise reducer 	Other Length armored cord from 12" to 72"(inches). Example: -ACH12 12" Long	ACHW -White Handset ACHR -Red Handset (Black is standard)	Coiled cord available from 5', 10', & 15' (feet). Example: -CCH5 5' Long	Ring Indicator Light located on the phone panel for visual ring indication	Ring Indicator Flashing Blue Light (Requires AC Power)



Providing Telecommunication Solutions Since 1930

Communication Equipment
& Engineering Company

<http://www.ceeco.net>
Email: sales@ceeco.net

519 SW Park Street
Okeechobee, FL

Voice 863-357-0798
Fax 863-357-0006