



Tripp Lite
 1111 West 35th Street
 Chicago, IL 60609 USA
 Telephone: +(773) 869 1234
 E-mail: saleshelp@tripplite.com

Model #: SR4POST13

13U 4-Post SmartRack Open Frame Rack - Organize and Secure Network Rack Equipment



Highlights

- 13U 4-post open frame rack
- Black steel with square, numbered mounting holes
- Toolless button holes to accept PDUs or cable managers

Description

SmartRack 4-post open frame racks are ideal for cost conscious 19 inch rack mount applications. Multiple units can be bolted together side by side.

Package Includes

- SR4POST13
- Installation hardware
- 16x M6 cagenuts, screws, washers
- Cable management hooks
- Owner's manual with warranty information

Features

- Supports 1000lbs of rackmount equipment
- Adjustable mounting depth (22 to 39 inches)
- Textured powder coat finish
- Heavy-duty cold-rolled steel construction
- Numbered mounting positions
- Bolt down provisions
- Self squaring design
- Black finish
- Easy assembly
- Five year repair or replacement warranty

Specifications

PHYSICAL	
Installed whole system maximum rack depth (inches)	39.3

Installed whole system minimum rack depth (inches)	22
Installed whole system total rack space height (rack spaces)	13U
Shipping weight (lbs)	40
Shipping weight (kg)	18
Unit Dimensions (HWD/cm)	71.12 x 51.3 x 55.9~99.06 (depth adjustable)
Shipping Dimensions (HWD/in)	4.13 x 5.71 x 43.3
Shipping Dimensions (HWD/cm)	10.5 x 14.5 x 109.98
Unit weight (lbs)	39
Unit weight (kg)	17.55
Unit Dimensions (in)	28 x 20.20 x 22~39 (depth adjustable)
Color	Black
Weight Capacity - Stationary (lbs)	1000
SPECIAL FEATURES	
Grounding lug	Includes nuts, bolts, and washers to attach to user-supplied ground wire
CERTIFICATIONS	
NOM (Mexico)	Tested to NOM (Mexico)
Approvals	EIA-310-D, IEC 60297-3-100, DIN 41494, RoHS
WARRANTY	
Product Warranty Period (U.S., Canada & Puerto Rico)	5-year limited warranty

Related Items

Optional Products

Product Type	Related Model	Description	Qty.
KVM Switches & Accessories	B020-U08-19-IP	Console KVM Switch - 8-Port NetDirector 1U Rackmount Console IP KVM Switch w/17" LCD	1
KVM Switches & Accessories	B040-008-19	NetController 19" VGA Console KVM Switch - 8 Port	1
KVM Switches & Accessories	B040-016-19	NetController 19" VGA Console KVM Switch - 16 Port	1
Patch Panels	N252-012	12-Port Cat6 Patch Panel 568B	1
Patch Panels	N252-024	24-Port Cat6 Patch Panel 568B	1
Patch Panels	N252-048	48-Port Cat6 Patch Panel 568B	1
Rack Accessories	SR1UPANEL10	1U Blanking Panel Kit (10 pieces; toolless mounting.)	1
Rack Accessories	SR1UPANEL50	1U Blanking Panel Kit (50 pieces; toolless mounting.)	1

Rack Accessories	SRBOLTDOWN	Bolt-Down Kit (Secures included stabilizing brackets or optional stabilizing plates to facility floor.)	1
Rack Accessories	SRCABLEDUCT1U	1U Horizontal Cable Manager (Finger duct with cover.)	1
Rack Accessories	SRCABLEDUCTVRT	6-ft. (1.8 m) Vertical Cable Manager (Double finger duct with cover; toolless mounting.)	1
Rack Accessories	SRCABLELADDER	10-ft. x 1-ft. (3 m x 0.3 m) Cable Ladder (Includes 2 sections; requires SRCABLETRAY.)	1
Rack Accessories	SRCABLERING1U	1U Horizontal Cable Manager (Flexible ring type.)	1
Rack Accessories	SRCABLERING2U	2U Horizontal Cable Manager (Flexible ring type.)	1
Rack Accessories	SRCABLERINGVRT	6-ft. (1.8 m) Vertical Cable Manager (Flexible ring type; toolless mounting.)	1
Rack Accessories	SRCAGENUTS	Square Hole Hardware Kit (Includes 50 M6 screws and washers.)	1
Rack Accessories	SRCASTER	Heavy-Duty Rolling Caster Kit (Includes 4 casters. Casters are included with 48/42/25U enclosures.)	1
Rack Accessories	SRFAN3U	3U Fan Panel, 120V (3 high-performance fans; 210 CFM; 5-15P plug.)	1
Rack Accessories	SRSHELF2P	2U Cantilever Fixed Shelf (60 lb / 27 kg capacity; 18-in. / 457 mm depth.)	1
Rack Accessories	SRSHELF4PHD	Heavy-Duty Fixed Shelf (250 lb / 113 kg capacity; 26 in / 660 mm depth.)	1
Rack Accessories	SRSHELF4PKYBD	Keyboard Shelf (25 lb / 11 kg capacity; 16-in. / 406 mm depth.)	1
Rack Accessories	SRSHELF4PSL	Standard Sliding Shelf (50 lb / 22 kg capacity; 26 in/ 660 mm depth.)	1
Rack Accessories	SRSHELF4PSLHD	Heavy-Duty Sliding Shelf (100 lb / 45 kg capacity; 26 in / 660 mm depth.)	1
Rack Accessories	SRXFAN3U	3U Fan Panel, 230V (3 high-performance fans; 210 CFM; C14 inlet.)	1
Rack Accessories	UPSHDEARKIT	Heavy-Duty Mounting Ear Kit (Supports 2U cabinets up to 65 lb / 29 kg from front vertical rails in 4-post or 2-post racks and enclosures.)	1
Rackmount Consoles	B021-000-17	Rackmount Console - 1U Rackmount Console with 17" LCD	1
Rackmount Consoles	B021-000-19	Rackmount Console - 1U Rackmount Console with 19" LCD	1

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=4025.

Copyright © 2012 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.