



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: PDU1215

Single-Phase Basic PDU, 15A 120V, 1U Horizontal Rackmount, NEMA 5-15R outlets, NEMA 5-15P input plug

Highlights



- Basic single phase 15A 120V PDU
- 1U horizontal rackmount installation
- NEMA 5-15P input; 15 ft. / 4.5m line cord
- 13 NEMA 5-15R outlets (1 front / 12 rear)
- Reversible housing; 4.5 in. / 11.4 cm depth

Description

Tripp Lite Basic Power Distribution Units / PDU systems offer reliable rackmount power distribution. Supplies equipment with continuous power from any protected UPS, generator or mains input power source. High quality design includes rugged all-metal housing and secure rackmount installation with included mounting accessories.

Applications

- Multi-outlet power distribution unit is the ideal means of powering multiple loads in 19 inch rackmount, wallmount and under-counter applications, such as internetworking, PC systems, telecommunications, audio/video, security, sound reinforcement and more. Ideal for distribution of UPS, generator or commercially derived AC power to protected equipment.

Package Includes

- PDU1215 Rackmount Power Strip
- Warranty information
- Instruction manual

Features

- 15A single phase 120V Basic Power Distribution Unit / PDU
- Attached NEMA 5-15P 15A 120V input plug with 15 ft. / 4.5m line cord
- 1U horizontal rackmount format installs in one rack space
- 13 NEMA 5-15R outlets (1 front facing / 12 rear)
- Mounting flanges support installation in 2 and 4 post racks, with additional support for wall-mount and under-counter installation formats
- Optional PDUSIDEBRKT enables 0U vertical rackmount in compatible racks
- Back panel grounding lug
- Lifetime limited warranty

Specifications

OVERVIEW	
Model Type	Basic
PDU Type	Basic
OUTPUT	

Frequency compatibility	50 / 60 Hz
Output nominal voltage	120V
Overload protection	15A
Outlet quantity / type	13 NEMA 5-15R
INPUT	
PDU Input Voltage	100; 120; 127
Recommended Electrical Service	120V
Maximum Input Amps (A)	15
Input connection type	NEMA 5-15P
Plug Type	NEMA 5-15P (15A 120V)
PDU Plug Type	NEMA 5-15P
Input cord length (ft.)	15
Voltage compatibility (VAC)	120
Phase	Single-Phase
LEDS ALARMS & SWITCHES	
Switches	No power switch
PHYSICAL	
Unit Dimensions (HWD/in)	1.75 (1U) x 17.5 x 4.5
Unit Dimensions (HWD/cm)	4.5 x 44.5 x 11.4
Material of construction	Sheet metal
Style	Rackmount, Vertical Rackmount, Wallmount/Under-Counter
Form factors supported	1U rackmount, 0U vertical rackmount, wall-mount and undercounter installation supported
PDU Form Factor	Horizontal (1U, 2U, etc)
Outlets center to center measurement	30.2mm
SPECIAL FEATURES	
TVSS grounding	Back panel nut and bolt grounding lug
CERTIFICATIONS	
Certifications	Tested to UL60950-1 (USA), CSA-C22.2 (Canada)
WARRANTY	
Product Warranty Period (U.S., Canada & Puerto Rico)	Lifetime limited warranty

Related Items

Optional Products

Product Type	Related Model	Description	Qty.
--------------	---------------	-------------	------

Power Cables	P002-002	2-ft. Power Cord (IEC-320-C14 to NEMA 5-15R)	1
Power Cables	P007-002	2-ft. Heavy-Duty 14AWG Power cord (IEC-320-C13 to NEMA 5-15P)	1
Power Cables	P007-006	6-ft. Heavy-Duty 14AWG Power cord (IEC-320-C13 to NEMA 5-15P)	1
Power Cables	P007-010	10-ft. Heavy-Duty 14AWG Power cord (IEC-320-C13 to NEMA 5-15P)	1
Power Cables	P010-012	12-ft. 18AWG Power cord (NEMA 5-15P to IEC-320-C13)	1
Power Cables	P012-006	6-ft. Notebook Power cord (NEMA 1-15P to IEC-320-C7)	1
Power Cables	P022-001	1-ft. 18AWG Power Extension cord (NEMA 5-15R to NEMA 5-15P)	1
Power Cables	P023-001	1-ft. 14AWG Power Adapter cord (NEMA L5-15R to NEMA 5-15P)	1
Power Cables	P034-010	10-ft. 14AWG Heavy Duty Power cord (IEC-320-C19 to NEMA 5-15P)	1
Rackmount/Wallmount Kits	PDUSIDEBRKT	Enables Vertical Installation of Select 1U PDUs, Power Strips and Surge Suppressors in SmartRack Configurations	1

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=2004.

Copyright © 2012 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.