



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: PDU2430

Single-Phase Basic PDU, 30A 120V, 1U Horizontal Rackmount, NEMA 5-15R outlets, NEMA L5-30P input plug

Highlights



- Basic single phase 30A 120V PDU
- 1U horizontal rackmount installation
- NEMA L5-30P input; 15 ft. / 4.5m line cord
- 24 5-15R outlets (12 front / 12 rear)
- Reversible housing; 4.5 in. / 11.4cm depth

Description

Tripp Lite Basic Power Distribution Units / PDU systems offer reliable rackmount power distribution. Supplies equipment with continuous power from any protected UPS, generator or mains input power source. High quality design includes rugged all-metal housing and secure rackmount installation with included mounting accessories.

Applications

- Multi-outlet power distribution unit is the ideal means of powering multiple loads in 19 inch rackmount, wallmount and under- counter applications, such as inter-networking, PC systems, telecommunications, audio/video, security, sound reinforcement and more. Ideal for distribution of UPS, generator or commercially derived AC power to protected equipment.

Package Includes

- PDU2430 Rackmount Power Strip
- Warranty information
- Instruction manual

Features

- 30A single phase 120V Basic Power Distribution Unit / PDU
- Attached NEMA L5-30P 30A 120V input plug with 15 ft. / 4.5m line cord
- 1U horizontal rackmount format installs in one rack space
- 24 NEMA 5-15R outlets (12 front / 12 rear)
- Mounting flanges support installation in 2 and 4 post racks, with additional support for wall-mount and under-counter installation formats
- Optional PDUSIDEBRKT enables 0U vertical rackmount in compatible racks
- Back panel grounding lug

Specifications

OVERVIEW	
Model Type	Basic
PDU Type	Basic
OUTPUT	

Frequency compatibility	50 / 60 Hz
Output VA	2880
Output nominal voltage	120V
Overload protection	30A
Outlet quantity / type	24 NEMA 5-15R
INPUT	
PDU Input Voltage	100; 120; 127
Recommended Electrical Service	120V
Maximum Input Amps (A)	30
Maximum Input Amps (A) Details	Agency de-rated to 24A
Input connection type	NEMA L5-30P
Plug Type	NEMA L5-30P (30A 120V)
PDU Plug Type	NEMA L5-30P
Input cord length (ft.)	15
Voltage compatibility (VAC)	120
Phase	Single-Phase
LEDS ALARMS & SWITCHES	
Switches	No power switch
PHYSICAL	
Unit Dimensions (HWD/in)	1.75 (1U) x 17.5 x 4.5
Unit Dimensions (HWD/cm)	4.4 x 44.5 x 11.1
Material of construction	Sheet metal
Style	Rackmount, Vertical Rackmount, Wallmount/Under-Counter
Form factors supported	1U rackmount, 0U vertical rackmount, wall-mount and undercounter installation supported
PDU Form Factor	Horizontal (1U, 2U, etc)
Outlets center to center measurement	Distance between Front outlets = 30.2mm; Distance between Rear outlets = 30.2mm
SPECIAL FEATURES	
TVSS grounding	Back panel nut and bolt grounding lug
CERTIFICATIONS	
Certifications	Tested to UL60950-1 (USA) and CAN/CSA C22.2 No. 60950-1-03 (Canada)
WARRANTY	
Product Warranty Period (U.S., Canada & Puerto Rico)	Lifetime limited warranty

Related Items

Optional Products

Product Type	Related Model	Description	Qty.
Power Cables	P007-002	2-ft. Heavy-Duty 14AWG Power cord (IEC-320-C13 to NEMA 5-15P)	1
Power Cables	P007-006	6-ft. Heavy-Duty 14AWG Power cord (IEC-320-C13 to NEMA 5-15P)	1
Power Cables	P007-010	10-ft. Heavy-Duty 14AWG Power cord (IEC-320-C13 to NEMA 5-15P)	1
Power Cables	P010-012	12-ft. 18AWG Power cord (NEMA 5-15P to IEC-320-C13)	1
Power Cables	P012-006	6-ft. Notebook Power cord (NEMA 1-15P to IEC-320-C7)	1
Power Cables	P022-001	1-ft. 18AWG Power Extension cord (NEMA 5-15R to NEMA 5-15P)	1
Power Cables	P023-001	1-ft. 14AWG Power Adapter cord (NEMA L5-15R to NEMA 5-15P)	1
Power Cables	P034-010	10-ft. 14AWG Heavy Duty Power cord (IEC-320-C19 to NEMA 5-15P)	1

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=2460.

Copyright © 2012 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.