

T40L9C2



Article Number: 111-04300

Standard Cable Tie, 14.6" Long, 40lb Tensile Strength, PA66, Natural, 100/pkg

 RoHS

 Download drawing

 Download spec sheet

Base Data

|                               |                                                                                                                                                                                                                                                                                                                                                                                       |
|-------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Local Order Number            | T40L9C2                                                                                                                                                                                                                                                                                                                                                                               |
| Type                          | T40L                                                                                                                                                                                                                                                                                                                                                                                  |
| Color                         | Natural (NA)                                                                                                                                                                                                                                                                                                                                                                          |
| Features and Benefits         | <ul style="list-style-type: none"><li>• Inside serrations allow for strong hold on cables and wire bundles.</li><li>• Head design provides high tensile strength with very low insertion force.</li><li>• Bent tail ensures a quick and simple installation.</li></ul>                                                                                                                |
| Product Description           | HellermannTyton standard cable ties feature inside serrations providing a positive hold onto wire and cable bundles. The head design guarantees high tensile strength, as well as a low insertion force. The bent tail design allows quick and simple installations by hand. For high volume applications, tensioning tools are available to ensure consistent and safe installation. |
| Fixation Method (FF)          | None                                                                                                                                                                                                                                                                                                                                                                                  |
| Identification Plate Position | none                                                                                                                                                                                                                                                                                                                                                                                  |
| Releasable Closure (Yes/No)   | No                                                                                                                                                                                                                                                                                                                                                                                    |
| Variant                       | Inside Serrated                                                                                                                                                                                                                                                                                                                                                                       |
| Short Description             | Standard Cable Tie, 14.6" Long, 40lb Tensile Strength, PA66, Natural, 100/pkg                                                                                                                                                                                                                                                                                                         |

Product Dimensions

|                                     |          |
|-------------------------------------|----------|
| Minimum Tensile Strength (Imperial) | 40.0 lbs |
| Minimum Tensile Strength (Metric)   | 180.0 N  |
| Length L (Imperial)                 | 14.6 "   |
| Length L (Metric)                   | 370.0 mm |
| Width W (Imperial)                  | 0.16 "   |
| Width W (Metric)                    | 4.0 mm   |
| Bundle Diameter Min. (Imperial)     | 0.06 "   |
| Bundle Diameter Min. (Metric)       | 1.5 mm   |
| Bundle Diameter Max. (Imperial)     | 4.13 "   |
| Bundle Diameter Max. (Metric)       | 105.0 mm |

Logistics and Packaging

|                           |      |
|---------------------------|------|
| Quantity Per              | bag  |
| Package Quantity (Metric) | 100  |
| Carton Quantity           | 5000 |

Material and Specifications

|                                       |                                  |
|---------------------------------------|----------------------------------|
| <b>Material</b>                       | Polyamide 6.6 (PA66)             |
| <b>Material Shortcut</b>              | PA66                             |
| <b>CSA Certified</b>                  | No                               |
| <b>Flammability</b>                   | UL94 V2                          |
| <b>Halogenfree</b>                    | Yes                              |
| <b>Operating Temperature</b>          | -40°F to +185°F (-40°C to +85°C) |
| <b>ROHS compliant (Article 4 - 1)</b> | Yes                              |
| <b>Certification/Specification</b>    | UL ZODZ2.E64139                  |
| <b>UL Listed (US and Canada)</b>      | Yes                              |
| <b>UL Recognized (US and Canada)</b>  | Yes                              |