

MB4SHA10C2



**Article Number:** 151-29203

**Adhesive Bases, .18" Max tie width, .15" Hole Dia., 1.12" Length/Width, PA66, White, 100/pkg**

 **RoHS**



[Download spec sheet](#)

Base Data

|                       |                                                                                                                                                                                                                                                                     |
|-----------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Local Order Number    | MB4SHA10C2                                                                                                                                                                                                                                                          |
| Type                  | MB4SHA                                                                                                                                                                                                                                                              |
| Color                 | White (WH)                                                                                                                                                                                                                                                          |
| Features and Benefits | <ul style="list-style-type: none"><li>• 2-way opening for use with 18 through 50 pound cable ties to provide stability when securing bundles.</li><li>• Secures using the adhesive backing and/or with one screw.</li></ul>                                         |
| Product Description   | HellermannTyton's 2 way, adhesive fastened mounting base is used with 18 through 50 pound cable ties to provide stability when securing bundles. The mounts are installed using the adhesive backing and/or by inserting one screw through the center of the mount. |
| Fixation Method (FF)  | Screw Mounting and Adhesive                                                                                                                                                                                                                                         |
| Short Description     | Adhesive Bases, .18" Max tie width, .15" Hole Dia., 1.12" Length/Width, PA66, White, 100/pkg                                                                                                                                                                        |

Product Dimensions

|                                     |         |
|-------------------------------------|---------|
| Length L (Imperial)                 | 1.12 "  |
| Length L (Metric)                   | 28.3 mm |
| Width W (Imperial)                  | 1.12 "  |
| Width W (Metric)                    | 28.3 mm |
| Cable Tie Width Max. (Imperial)     | 0.18 "  |
| Cable Tie Width Max. (Metric)       | 4.6 mm  |
| Height H (Imperial)                 | 0.23 "  |
| Height H (Metric)                   | 5.8 mm  |
| Mounting Hole Diameter D (Imperial) | 0.15 "  |
| Mounting Hole Diameter D (Metric)   | 3.9 mm  |
| Thickness of Adhesive TA (Imperial) | 0.031 " |
| Thickness of Adhesive TA (Metric)   | 0.8 mm  |

Logistics and Packaging

|                           |      |
|---------------------------|------|
| Quantity Per              | bag  |
| Package Quantity (Metric) | 100  |
| Carton Quantity           | 4000 |

Material and Specifications

|                   |                                                 |
|-------------------|-------------------------------------------------|
| Material          | Polyamide 6.6 (PA66)                            |
| Material Shortcut | PA66                                            |
| Adhesive          | Synthetic rubber with base of polyethylene foam |

|                                       |                                  |
|---------------------------------------|----------------------------------|
| <b>Adhesive Shortcut</b>              | Synthetic rubber T50             |
| <b>Adhesive Operating Temperature</b> | -4°F to +122°F (-20°C to +50°C)  |
| <b>CSA Certified</b>                  | No                               |
| <b>Flammability</b>                   | UL94 V2 (excluding adhesive)     |
| <b>Operating Temperature</b>          | -40°F to +185°F (-40°C to +85°C) |
| <b>ROHS compliant (Article 4 - 1)</b> | Yes                              |
| <b>UL Listed (US and Canada)</b>      | No                               |
| <b>UL Recognized (US and Canada)</b>  | Yes                              |