




GTM100A0C2



Article Number: 130-91001

Grip Tie Mount for .75" Wide Grip Tie, Adhesive, PA66UV, Black, 100/pkg

 **RoHS**



[Download spec sheet](#)

Base Data

Local Order Number	GTM100A0C2
Type	GTM100A
Color	Black (BK)
Features and Benefits	• Adhesive with 1/4" screw hole mount secures .75" grip ties for use on flat surfaces
Product Description	To secure bundles to flat surfaces, HellermannTyton offers a mounting base to be used with the Grip Ties. Available with or without adhesive, two sizes of Grip Tie mounts cover every size of Grip Tie. The mounts are manufactured from nylon 6/6 material and are UV-stabilized for outdoor applications.
Fixation Method (FF)	None
Identification Plate Position	none
Mounting Method	Adhesive
Releasable Closure (Yes/No)	Yes
Tie Closure	hook and loop
Variant	Grip Tie
Short Description	Grip Tie Mount for .75" Wide Grip Tie, Adhesive, PA66UV, Black, 100/pkg

Product Dimensions

Length L (Imperial)	3.25 "
Length L (Metric)	82.55 mm
Width W (Imperial)	1.5 "
Width W (Metric)	38.1 mm

Logistics and Packaging

Quantity Per	bag
Package Quantity (Imperial)	100
Package Quantity (Metric)	100 Pieces

Material and Specifications

Material	Polyamide 6.6 UV-resistant (PA66UV)
Material Shortcut	PA66UV
ROHS compliant (Article 4 - 1)	Yes

