




CTM310C2



Article Number: 151-30605

Cable Tie Mount, 0.2" Hole Dia., 0.31" Max Tie Width, PA66, White, 100/pkg

 RoHS

 Download spec sheet

Base Data

| | |
|-----------------------|---|
| Local Order Number | CTM310C2 |
| Type | CTM3 |
| Color | White (WH) |
| Features and Benefits | <ul style="list-style-type: none">• Designed for use with 18 through 120 pound cable ties to provide stability when securing bundles.• Secures with a single screw providing quick installation. |
| Product Description | HellermannTyton cable tie mounts are designed for use with 18 through 120 pound cable ties to provide stability when securing bundles. The mounts are installed quick and easy by securing a single screw. |
| Fixation Method (FF) | Screw Mounting and Rivet |
| Short Description | Cable Tie Mount, 0.2" Hole Dia., 0.31" Max Tie Width, PA66, White, 100/pkg |

Product Dimensions

| | |
|-------------------------------------|---------|
| Length L (Imperial) | 0.86 " |
| Length L (Metric) | 21.8 mm |
| Width W (Imperial) | 0.61 " |
| Width W (Metric) | 15.5 mm |
| Cable Tie Width Max. (Imperial) | 0.31 " |
| Cable Tie Width Max. (Metric) | 7.9 mm |
| Height H (Imperial) | 0.37 " |
| Height H (Metric) | 9.4 mm |
| Mounting Hole Diameter D (Imperial) | 0.2 " |
| Mounting Hole Diameter D (Metric) | 5.1 mm |

Logistics and Packaging

| | |
|---------------------------|------------|
| Quantity Per | bag |
| Package Quantity (Metric) | 100 Pieces |

Material and Specifications

| | |
|--------------------------------|----------------------------------|
| Material | Polyamide 6.6 (PA66) |
| Material Shortcut | PA66 |
| Flammability | UL94 V2 |
| Operating Temperature | -40°F to +185°F (-40°C to +85°C) |
| ROHS compliant (Article 4 - 1) | Yes |
| Certification/Specification | UL |

UL Listed (US and Canada) No

UL Recognized (US and Canada) Yes