

QTTIEOHS



Article Number: 105-00001

Cable Tie for QS101 - Black Color, 18lb, 5000 Ties per Reel, 2 Reels per Carton

 RoHS



[Download spec sheet](#)

Base Data

Local Order Number	QTTIEOHS
Type	QTTIEOHS
Color	Black (BK)
Features and Benefits	HellermannTyton's automatic cable tie tool systems are compact, fast, reliable, and versatile, accommodating a variety of wiring harness, and bundling and securing requirements. These tool systems are designed to provide significant labor and cost savings through process improvements, lower installed costs and greater consistency, quality and ergonomic benefits.
Identification Plate Position	none
Releasable Closure (Yes/No)	No
Short Description	Cable Tie for QS101 - Black Color, 18lb, 5000 Ties per Reel, 2 Reels per Carton

Product Dimensions

Minimum Tensile Strength (imperial)	18.0 lbs
Minimum Tensile Strength (N)	80 N
Length L (imperial)	3.94 "
Length L (metric)	100 mm
Width W (imperial)	0.1 "
Width W (metric)	2.5 mm
Bundle Diameter min (imperial)	0.03 "
Bundle Diameter min (metric)	0.7 mm
Bundle Diameter max (imperial)	0.63 "
Bundle Diameter max (metric)	16.0 mm
Thickness T (imperial)	0.043 "
Thickness T (Metric)	1.1 mm

Logistics and Packaging

Quantity per	reel
Package Quantity (imperial)	5000
Package Quantity	5000
Carton Quantity	10000
Reel Diameter (imperial)	18 "
Reel Diameter (metric)	457 mm
Reel Weight (metric)	2.18 kg
Reel Weight (imperial)	4.8 lbs

Reel Width (imperial) 5.2 "

Reel Width (metric) 132 mm

Material and Specifications

Material Polyamide 6.6 heat and UV stabilized (PA66HSUV)

Material Shortcut PA66HSUV

Flammability UL94 V2

Operating Temperature -40°F to +230°F (-40°C to +110°C)

ROHS Conformity Yes

UL Listed (US and Canada) Yes