

12VDC high temperature
power supply for stand-alone units



Description

The ComNet™ PS12DC-HT power transformer supplies 12V DC power to ComNet™ stand-alone units. The PS12DC-HT operates on 100-240 VAC. The PS12DC-HT is provided for installations with high ambient temperatures.

Features

- Universal power input, 100-240 VAC
- High temperature operating range
- Lifetime Warranty

specifications


ELECTRICAL & MECHANICAL

Power:	
Input:	100-240 VAC, 50-60 Hz @ 0.6 A Max.
Output:	12 VDC @ 1.5 A Max.
Size (in./cm) (L×W×H) (excluding line cord)	4.53 × 1.77 × 1.22 in., (11.5 × 4.5 × 3.1 cm)
Shipping Weight:	<0.5 lb./0.25 kg

ENVIRONMENTAL

MTBF:	>100,000 hours
Operating Temp:	0° C to +75° C
Relative Humidity:	20% to 90% (non-condensing)

PART NUMBER	DESCRIPTION
PS12DC-HT-EU PS12DC-HT-UK	12VDC High Temperature PSU



Complies with FDA Performance Standard for Laser Products, Title 21, Code of Federal Regulations, Subchapter J
In a continuing effort to improve and advance technology, product specifications are subject to change without notice.