



# exacqVision **LC-Series**

## IP & Hybrid Appliance *Analog and IP Cameras*

### Key Features & Benefits:

- **All-In-One Solution** — Video recording, web/mobile client hosting and local live video display from the same desktop appliance. Available in hybrid NVR (analog and IP cameras) and IP NVR (IP cameras) models.

- **Up to 32 Cameras Per Appliance** — Up to 16 analog and up to 16 IP cameras per appliance. Compatible with over 1,000 IP camera models. Continuously record up to 100Mbps of video.


- **Powerful, Easy-to-Use VMS Included** — Powerful, pre-loaded with exacqVision Start VMS software that does the following:

- Auto detects IP cameras for quick, simple setup
- Easily add additional IP cameras--up to 16 total
- Continuous motion, time or alarm-based recording configurable per camera
- Search recorded video with a graphical thumbnail search and playback multiple cameras simultaneously
- View an instant replay of video from any camera with exacqReplay
- Easily control PTZ cameras
- Export audio, video and pictures to be easily e-mailed or saved

- **Local, Remote, Web, Mobile User Interfaces** — Access live and recorded video on multiple client PCs with free Windows, Mac or Linux client application. exacqVision web server application is pre-installed on the server to access video through web browser or free exacqVision iOS and Android apps.

- **3-Year Warranty and Software Subscription Agreement (SSA)** — 3-year hardware warranty and SSA included. Update client, appliance and web appliance software with the latest exacqVision software features at no additional cost during the 3-year period.



Analog Settings	IPS	Hybrid
Analog Inputs		8/16
Analog Compression		H.264
Analog Frame Rate (NTSC)		240/480
Analog Frame Rate (PAL)		200/400
Analog Outputs		1 mux , BNC
Alarm Inputs	16 (optional external)	8 (optional external)
Alarm Outputs	4TTL, 1 relay output (Optional external)	3 TTL, 1 Relay (Optional external)
Audio Inputs		8/16
IP Settings		
IP Cameras	4 IP licenses included. Expandable to 16 cameras per server (data rate dependent)	
Server Features		
Pre-Loaded VMS Software	exacqVision Start (standard), exacqVision Professional or Enterprise Server (optional)	
Typical Video Storage Rate	150 Mbps	
Local Client Display Rate	180 FPS	
Max Hard Drives	1	
Storage Maximum (Internal)	4TB	
Server Operating System	Ubuntu Linux 10.04	
Monitor Output	DVI-D, VGA	
NIC	1 x 1 Gbps	
USB2 Ports	8 x USB 2.0 (2 front, 6 rear)	
Keyboard & Mouse	Mouse and on-screen keyboard included	
Size		
Dimensions (l x w x h)	10.8 x 11.5 x 2.5 in 27.5 x 29.4 x 6.5 cm	
Weight	11 – 15 lbs. 5 – 6.8 kg	
General		
Regulatory	CE, FCC	
Warranty	3 years, parts & labor plus 3 years SSA included 	
Input Voltage	120/240 VAC auto-sensing	
Power & Heat	50 Watts/170 BTU/h (Max) 40 Watts/135 BTU/h (Typical)	60 Watts/205 BTU/h (Max) 50 Watts/170 BTU/h (Typical)
Operating Temperature	40° – 95°F (4.5° – 35°C)	

All part numbers can be found in the product catalog at: <https://exacq.com/catalog/>

Specifications subject to change. Visit [www.exacq.com](http://www.exacq.com) for the most current product specifications.