

Smart 108 SPU - 8-Port Cat5 KVM Switch for Rack Environments

MODEL NUMBER: 0SU22181



Description

Save Space and Money

The Smart 108 SPU is a single-user analog Cat5 KVM switch that gives you the ability to control multiple computers or servers from a single keyboard/video/mouse console. The rack mountable, 1U-sized switch features innovative ROC (RICC on cable) dongle technology that directly connects you to each server in the rack, eliminating cable clutter and the need for multiple consoles.

From SOHO to Enterprise

The Smart 108 SPU is ideal for multiple server environments, from the small home office to the enterprise data center. Whatever the application, a company operating several servers can now connect them all to a single keyboard, video and mouse console, and operate them with 30m/100ft of range between the server and switch.

Features

- 8 Ports
- BIOS level access
- Multilayer security
- Multi-platform – PS/2 and USB support
- Extends distance between servers and switch up to 30 meters/100 feet over Cat5e cabling
- Includes a USB to PS/2 adapter that allows you to use a USB keyboard and mouse on the console end
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

Highlights

- 8 Ports
- BIOS level access
- Multilayer security
- Multi-platform – PS/2 and USB support
- Extends distance between servers and switch up to 30 meters/100 feet over Cat5e cabling
- Includes a USB to PS/2 adapter that allows you to use a USB keyboard and mouse on the console end
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

System Requirements

Operating System

- DOS, Windows, LINUX, UNIX, MAC and all other major operating systems

Console

- VGA Monitor
- USB or PS/2 Keyboard and Mouse

Resolution

- Supports video resolutions up to 1600 x 1200 @ 75Hz

Package Includes

- Smart 108 SPU
- USB to PS/2 Adapter
- RS232 Cable
- Power Cord
- Rackmount Hardware
- Owner's Manual



OVERVIEW	
Users	1
Console	No
Port Control	Push Buttons, Hotkeys, OSD
PC/Server Connections	VGA; USB; PS/2
Cat5 KVM Switch	Yes
IP Remote Access	Yes
Style	1U Rackmount
Model Type	KVM Switches
PHYSICAL	
Unit Dimensions (hwd / in.)	1.63 x 8.46 x 4.8
Unit Dimensions (hwd / cm)	4.15 x 21.5 x 12.2
Unit Weight (lbs.)	4.1
Unit Weight (kg)	1.87
Color	Black
ENVIRONMENTAL	
Storage Temperature Range	-40 to 70 C / -40 to 158 F
Relative Humidity	80% Non-Condensing
Operating Temperature	0 to 40 C / 32 to 104 F
CONNECTIONS	
Ports	8
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.