

## 8-Port 1U Rack-Mount DVI / USB KVM Switch with Audio and 2-port USB Hub

MODEL NUMBER: **B043-DUA8-SL**



### Description

Tripp Lite's B043-DUA8-SL, NetController 8-Port, 1U rackmount DVI / USB / Audio KVM Switch is an affordable, highly-flexible enterprise class KVM Switch. Control up to 8 directly connected computers, or expand the number of connected computers to up to 64, by cascading up to 8 additional B043-DUA8-SL KVM switches. Switch between connected computers via pushbuttons or keyboard hot-key commands. Other features include: Audio Support, 2-Port USB Hub for peripheral sharing among switched computers, and DVI Single Link resolution at 1920x1200. Mounts easily in a standard 19" rack/cabinet and includes all necessary mounting hardware. Compatible with all major operating systems. Constructed of heavy-duty steel housing.

Order [P759 Series cables](#) separately, in 6ft, 10ft, and 15ft lengths.

### Features

- Directly connect up to 8 computers with DVI, USB, and audio.
- Expand the number of connected computers by cascading an additional level of KVM switches.
- Supports 2.1 Channel Stereo Audio and microphone.
- (x2) USB 2.0 ports for sharing peripherals among connected computers.
- USB hub functionality can be unbinded from the KVM, allowing users to access one computer while the USB hub focus remains on another computer.
- Switch between connected computers via pushbuttons or hotkey commands.
- DVI-I Single-Link supports digital video resolutions up to 1920 x 1200, and analog video resolutions up to 2048 x 1536.
- Auto Scan mode lets users scan connected computers without having to manually switch between them.
- Multi-platform support – compatible with all major operating systems.
- Plug and play setup – no software installation required.
- Supports EDID (Extended Display Identification Data) transmission to connected computers for optimal display performance.
- Supports HDMI and VGA monitors with appropriate adapters...see "System Requirements"

### Highlights

- NetController 8-Port, 1U rackmount KVM switch
- Control 8 computers via a single DVI monitor and USB keyboard/mouse
- Control up to 64 computers by cascading up to 8 additional B043-DUA8-SL KVM switches
- Compatible with all major operating systems

### System Requirements

- DVI , HDMI\*, or VGA\*\* monitor
- USB mouse and keyboard
- Computer with a DVI or VGA\* port
- Computer with a USB port
- [P759-Series DVI-D/USB/Audio KVM cable kit](#) for each connected computer
- Microphone with a 3.5 mm Male connector (if using the microphone feature)
- Speakers with a 3.5 mm Male connector (if using the speaker feature)
- Compatible with all major operating systems

\*Requires [DVI to HDMI adapter](#)

\*\*Requires a [DVI to VGA adapter](#)

### Package Includes

- B043-DUA8-SL KVM Switch
- External Power Supply (Input: 100-240V, 50/60Hz; Output: 9V, 2A)
- Rackmount Hardware
- Owner's Manual



- Includes mounting hardware for 19" rackmount installations.

## Specifications

OVERVIEW	
Users	1
AC Adapter	DC 9V
Port Control	Push Buttons, Hotkeys
Max CPU	64
PC/Server Connections	DVI; USB; VGA
Cat5 KVM Switch	No
IP Remote Access	Yes
Style	1U Rackmount
PHYSICAL	
Unit Weight (lbs.)	5.30
Unit Weight (kg)	2.40
Color	Black
ENVIRONMENTAL	
Storage Temperature Range	-20 to +60C
Operating Temperature	0 - 40C
CONNECTIONS	
Ports	8
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.