

## 1-Port Plug-n-Play USB 2.0 over Cat5/Cat6 Extender Kit, Transmitter and Receiver, Hi-Speed USB up to 164-ft. (50M)

MODEL NUMBER: **B203-101-PNP**



### Description

Tripp Lite's B203-101-PNP, USB 2.0 over Cat5 Extender Kit, allows you to connect your USB-equipped Windows PC to a USB 2.0 or 1.1 peripheral or device up to 164 ft ( 50 meters ) away. This is especially useful for connecting a printer or other peripheral that is far away from your computer, but does not have network connectivity or is located in an area where the network is unavailable. The USB extender kit sends the USB signal from the transmitter to the receiver over a user-supplied Cat5/5e/6 cable. Transfer rates of up to 480Mbps at the maximum length. Compatible with Windows and Mac computerse. Plug and Play...no Drivers or Software required. Backwards compatible with USB 1.1 peripherals. For maximum signal integrity, use Cat5e Solid Conductor UTP cable. The USB extender kit's connectors and internal components are manufactured using high-quality materials suitable for use in demanding office, industrial, and commercial settings. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

### Features

- Connect a Hi-Speed USB 2.0 device up to 164 ft. ( 50m ) from your computer
- Uses readily available Cat5/Cat6 cable
- Includes a 1 ft. USB A/B device cable for connecting the local transmitter unit to a computer
- Supports Hi-Speed data transfer rates up to 480Mbps
- Plug and Play...no Drivers or Software required
- Compatible with Windows and Mac
- Backwards compatible with USB 1.1
- Before using with a touchscreen monitor, first confirm with the monitor manufacturer that USB 2.0 over Cat5 extenders are supported
- RoHS-compliant
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

## Specifications

### Highlights

- Connects a USB 2.0 or 1.1 peripheral up to 164 ft. from your Computer
- Plug and Play...no Drivers or Software required
- Windows and MAC compatible
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

### Applications

- Use with USB 2.0 peripherals that need to exceed the 16 ft. (5 m) distance limitation

### Package Includes

- Local transmitter unit with built-in USB cable
- Remote receiver unit
- External power supply ( Input: 100-240V, 50/60Hz, 0.5A Output: 5V, 2A )
- Owner's manual



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

OVERVIEW	
Chromebook Compatible	Yes
Style	USB
PHYSICAL	
Color	Black
ENVIRONMENTAL	
Storage Temperature Range	-20 to 60 C (-4 to 140 F)
Relative Humidity	20 to 90%
Operating Temperature	0 to 40 C (32 to 104 F)
CONNECTIONS	
Connector A	USB A (MALE)
Connector B	RJ45 (FEMALE)
Connector C	USB B (FEMALE)
Connector D	RJ45 (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.