

12V DC, 54-Amp Replacement Battery for HCRK-54 Medical-Grade Mobile Power Retrofit Kit

MODEL NUMBER: **BP12V54**



Highlights

- 12V DC, 54-Amp Replacement Battery for HCRK-54 Medical-Grade Mobile Power Retrofit Kit
- Sealed, Maintenance-Free

Applications

- Only to be used with the HCRK-54 Medical-Grade Mobile Power Retrofit Kit

Package Includes

- BP12V54 12V DC Battery
- Connection cable

Description

12V DC, 54-Amp Replacement Battery for HCRK-54 Medical-Grade Mobile Power Retrofit Kit. Sealed lead acid, maintenance-free, spill/leak proof, AGM battery, simple plug-in connection with included cable – Included in the HCRK-54. This is the replacement battery for the HCRK-54 battery.

Features

- 12V DC
- 54-Amp
- Simple plug-in connection with included cable
- Sealed, maintenance-free

Specifications

OVERVIEW	
Model Type	Batteries
Accessories Type	Battery
INPUT	
Voltage Compatibility (VDC)	12
PHYSICAL	
Unit Dimensions (hwd / in.)	6.500 x 8.750 x 10.000
Unit Dimensions (hwd / cm)	16.51 x 22.23 x 25.4
Unit Weight (lbs.)	44



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Unit Weight (kg)	19.96
WARRANTY	
Product Warranty Period (Worldwide)	6-month limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.