

Dual Desk Mount for 10" to 26" Flat-Screen Displays

MODEL NUMBER: **DDR1026SD**



Description

Tripp Lite's VESA-compliant DDR1026SD Dual Flat-Screen Desk Stand frees up valuable space in your workstation and increases workday productivity by enabling the suspension of 2 flat-panel displays on a single base. It features convenient one-touch display adjustment with tilt, swivel and rotation capabilities and fits most 10- to 26-inch flat-panel displays. Its durable, all-metal frame with scratch-resistant, powder-coat finish withstands the stress of repeated use and blends easily into any décor. It comes with all necessary mounting hardware, and each mount supports weights of up to 30 lbs. For peace of mind, the DDR1026SD comes backed by a 5-year warranty.

Features

- Tripp Lite's VESA-compliant DDR1026SD Dual Flat-Screen Desk Stand frees up valuable space in your workstation and increases workday productivity by enabling the suspension of 2 flat-panel displays on a single base
- Convenient one-touch display adjustment with tilt, swivel and rotation capabilities and fits most 10- to 26-inch flat-panel displays
- Durable, all-metal frame with scratch-resistant, powder-coat finish withstands the stress of repeated use and blends easily into any décor
- Includes all necessary mounting hardware, and each mount supports weights of up to 30 lbs
- 5-year warranty

Specifications

OVERVIEW	
Mounting Location	Desktop
PHYSICAL	
Unit Dimensions (hwd / in.)	15.7 x 28.9 x 10.2
Unit Dimensions (hwd / cm)	39.88 x 73.41 x 25.91
Unit Weight (lbs.)	8.5

Highlights

- Increases available desk/table space in office workstation applications
- Dual mounts fit most flat-panel displays from 10" to 26"
- Convenient one-touch display adjustment for easy view optimization and improved ergonomics
- Wide range of motion with -15° to +15° tilt, 180° swivel and 360° rotation capability
- Each mount supports up to 30 lbs.
- 5-year warranty

Package Includes

- DDR1026SD Full-Motion Flat-Screen Desk Mount
- Mounting Hardware
- Owner's Manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Unit Weight (kg)	3.86
Color	Black
Monitor Display Size (in.)	10 - 26
Monitor Display Size (cm)	25.4 - 66.04
VESA Pattern (mm)	75x75; 100x100
Motion	Full
Degrees of Motion	-15/+15 Tilt; 180 swivel; 360 rotate
Maximum Weight Capacity (lbs.)	30
Maximum Weight Capacity (kg)	13.61
FEATURES & SPECIFICATIONS	
Tools Necessary	Yes
Cord Management	Yes
WARRANTY	
Product Warranty Period (U.S. & Canada)	5-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.