

## Full-Motion Wall-Mount w/ Arms for 17" to 42" Flat-Screen Displays

MODEL NUMBER: DWM1737MA



### Description

Tripp Lite's VESA-compliant DWM1737MA Full-Motion Flat-Screen Wall Mount offers full-motion articulation and can free up valuable space in your workstation by allowing you to effortlessly reposition your display at any time, even after installation. Its sleek design features convenient one-touch display adjustment with tilt and swivel capabilities and fits most 17- to 42-inch flat-panel displays. Its durable, all-metal frame with scratch-resistant, powder-coat finish withstands the stress of repeated use and blends easily into any décor. It comes with all necessary mounting hardware and supports weights of up to 77 lbs. For peace of mind, the DWM1737MA comes backed by a 5-year warranty.

### Features

- Tripp Lite's VESA-compliant DWM1737MA Full-Motion Flat-Screen Wall Mount offers full-motion articulation and can free up valuable space in your workstation by allowing you to effortlessly reposition your display at any time, even after installation
- Sleek design features convenient one-touch display adjustment with tilt and swivel capabilities
- Fits most 17- to 42-inch flat-panel displays
- Durable, all-metal frame with scratch-resistant, powder-coat finish withstands the stress of repeated use and blends easily into any décor
- Includes all necessary mounting hardware and supports weights of up to 77 lb
- 5-year warranty

## Specifications

OVERVIEW	
Mounting Location	Wall
PHYSICAL	
Unit Weight (lbs.)	7.88

### Highlights

- **SEE NEW MODEL - DWM1742MA**
- Can be used to increase available desk/table space in office applications
- Fits most flat-panel displays from 17" to 42"
- Convenient one-touch display adjustment for easy view optimization
- Wide range of motion with -15° to +15° tilt, 180° swivel and -3° to +3° screen level adjustment capability
- Supports up to 77 lbs.
- 5-year warranty

### Package Includes

- DWM1737MA Full-Motion Flat-Screen Wall Mount
- Mounting Hardware
- Owner's Manual



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Unit Weight (kg)	3.57
Color	Black
Monitor Display Size (in.)	17 - 42
Monitor Display Size (cm)	43.18 - 106.68
VESA Pattern (mm)	75x75; 100x100; 200x100; 200x200
Motion	Full
Degrees of Motion	-15/+15 Tilt; 180 Swivel; -3/+3 Level Adjustment
Min/Max Arm Extension (in.)	2.21 min to 20.08 max
Min/Max Arm Extension (cm)	5.6 min to 51 max
Maximum Weight Capacity (lbs.)	77
Maximum Weight Capacity (kg)	35
<b>FEATURES &amp; SPECIFICATIONS</b>	
Tools Necessary	Yes
Cord Management	No
<b>WARRANTY</b>	
Product Warranty Period (U.S. & Canada)	5-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.