

Protect It! 12-Outlet Home/Business Theater Surge Protector, 10-ft. Cord, 2880 Joules

MODEL NUMBER: HT1210SAT3



Description

Tripp Lite's HT1210SAT3 Home/Business Theater Surge Suppressor provides advanced protection-- 2880 joules--stopping damaging surges and filtering disruptive line noise so components perform at their peak! You can see and hear the difference: sharper, crisper video; deeper, fuller audio and longer component life spans. Perfect for small-to-medium home/business theater installations: high-definition TVs, satellite and A/V receivers, DVD/CD players and more. 12 outlets (with transformer spacing and sliding safety covers), 3-line 2.2GHz coaxial protection and 1-line tel/modem/Ethernet (100BaseT, high-speed) protection safeguard an entire home/business theater system. \$250,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only). Includes two diagnostic LED, 10-ft. cord with a right-angle plug, 6-ft. gold DSS cable, 6-ft. phone cord and 6-ft. network cable.

Features

- 2880 joule surge suppression rating with EMI/RFI line noise filtering help components perform at their peak (sharper, crisper video; deeper, fuller audio and longer component life spans)
- 12 widely spaced surge-protected NEMA 5-15R AC outlets safeguard an entire home/business theater system while accommodating up to 4 large transformers without blocking outlets
- Sliding safety covers protect against accidental contact
- 3 sets of surge protected 2.2GHz gold coaxial connectors safeguard components on cable, satellite and antenna line; 6-ft gold DSS cable included
- 1-line tel/modem/ethernet (100BaseT, high speed) surge protection safeguards personal video recorders (PVRs) on a single dial-up or ethernet line. Built-in splitter (1 jack in and 2 jacks out) allows simultaneous connection of two devices sharing a single line; 6-ft phone and network cable included
- 10-ft cord with right angle NEMA 5-15P plug provides convenient location anywhere within a home/business theater system
- 2 diagnostic LEDs alert user to protection present (green) and grounded (red) status
- Keyhole slots provide convenient wall or cabinet mounting
- \$250,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Specifications

Highlights

- 12 outlets / 10-ft. cord
- 2880 joule rating
- 3-line 2.2GHz coaxial (gold) surge protection
- 1-line tel/modem/network (100BaseT, high-speed) surge protection
- \$250,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Applications

- Perfect for small-to-medium home/business theater installations: high-definition TVs, satellite and A/V receivers, DVD/CD players and more

Package Includes

- HT1210SAT3 Home/Business Theater Surge Suppressor
- 6-ft. gold coax cable, 6-ft. phone cord and 6-ft. network cable
- Instruction manual with warranty information



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

OVERVIEW	
Style	Strip
OUTPUT	
Frequency Compatibility	60 Hz
Output Receptacles	(12) 5-15R
Output (Watts)	1800
Circuit Breaker (amps)	15
Transformer Accommodation	Accommodates 4 transformers
USB Charging	No
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Connection Type	NEMA 5-15P
Input Plug Features	Space-saving right-angle input plug
Input Cord Length (ft.)	10
Input Cord Length (m)	3
Input Cord Gauge Type	14 gauge, SJT
Voltage Compatibility (VAC)	120
Maximum Surge Amps	180000
USER INTERFACE, ALERTS & CONTROLS	
Switches	Combination AC circuit breaker and 2-position on/off power switch
Diagnostic LEDs	Built-in LEDs confirm protection and grounding status
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	2880
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	150
UL1449 Let Through Rating	330, 400, 400
EMI / RFI Filtering	Up to 40 dB
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	Yes



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	Yes
Cable (Coax) Protection Details	3 line
Network (Ethernet) Protection	Yes
PHYSICAL	
Shipping Dimensions (hwd / in.)	2.05 x 8.6 x 13.39
Shipping Dimensions (hwd / cm)	5.21 x 21.84 x 34.01
Shipping Weight (lbs.)	2.51
Shipping Weight (kg)	1.14
Unit Dimensions (hwd / in.)	1.51 x 4.86 x 12.07
Unit Dimensions (hwd / cm)	3.84 x 12.34 x 30.66
Unit Weight (lbs.)	2.31
Unit Weight (kg)	1.05
Material of Construction	Plastic
Integrated Keyhole Mounting Tabs	Keyhole mounting slots allow desk or wall mounting
Color (AC Line Cord)	Black
Keyhole Slot Mounting Measurement (Center to Center)	Distance between horizontal tabs = 152mm; Distance between vertical tabs = 73.5mm
SPECIAL FEATURES	
Right-Angle Plug	Yes
CERTIFICATIONS	
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition
UL1363 (Power Tap)	UL1363
UL497A (Communications)	UL497A
FCC Part 68 (Communications)	FCC Part 68
cUL / CSA (Canada)	cUL
Approvals	Exceeds IEEE 587 category A&B specifications
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 Ultimate Lifetime Insurance



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Specifications are subject to change without notice. Photos may differ slightly from final products.