

Cat5e 350MHz Outdoor-Rated Patch Cable (RJ45M/M) - Gray, 50-ft.

MODEL NUMBER: **N007-050-GY**



Highlights

- High Quality Outdoor Rated PVC Jacket
- Molded, Snagless RJ45 Connector

Package Includes

- 50ft Outdoor Rated Cat5e Patch Cable

Description

Tripp Lite's line of Outdoor Rated Cat5e patch cables are manufactured with high quality UV (Ultra Violet) resistant PVC cable. With an Operating Temperature range of -40C to +60C (-40F to +140F), this 50ft cable handles a wide range of weather conditions, most importantly, the degrading effects of Ultra Violet rays. Molded, snagless connectors provide a secure connection every time. Cables meet EIA/TIA 568-B.2, and are UL verified to Category 5e.

Features

- UV (Ultra Violet) Resistant Gray PVC jacket
- CMR, CMX, and UL444 Rated
- EIA/TIA 568-B.2 Compliant
- UL Verified Category 5e
- Molded, Snagless Connectors
- 4pr, Solid Conductors for long distance signal integrity

Specifications

OVERVIEW	
Style	Cat5/5e
Model Type	Molded
Cable Types	CAT5/CAT5E
INPUT	
Cable Length (ft.)	50
Cable Length (m)	15.24



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

PHYSICAL	
Color	Gray
CONNECTIONS	
Connector A	RJ45 (MALE)
Connector B	RJ45 (MALE)
Number of Connectors	2
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.