

Cat5e 350MHz Bulk Solid-Core PVC Outdoor-Rated Cable - Gray, 1000-ft.

MODEL NUMBER: **N028-01K-GY**



Highlights

- UV Rated jacket prevents drying and cracking
- 4PR Solid conductors for Low Attenuation Loss
- CMX Outdoor rating; Temp range -40F to +140F

Applications

Excellent for running Cat5e cable to Outdoor Wireless Antennas

Package Includes

1000ft. Box Cat5e Outdoor Rated PVC Bulk Cable

Description

Tripp Lite's Outdoor Rated UV Resistant PVC Unshielded Cat5e cable is ideal for connecting to outdoor mounted wireless antennas. 4-pair, 24 AWG, solid conductors, handle long distance runs with low attenuation loss. Jacket is sequentially marked every two feet for easy measuring. Operating temperature range of -40C to +60C. UL1666 Riser and CMX Outdoor ratings. 1000-ft. Pull box; 26lbs. shipping weight. For pre-terminated patch cables, please browse "N007-" in the search box.

Features

- UV Rated jacket prevents drying and cracking
- 4PR Solid conductors for Low Attenuation Loss
- CMX Outdoor rating; Temp range: -40F to +140F
- 1000-ft. Pull-box, length marked every two feet
- Terminate with Tripp Lite N030-010 Solid wire Cat5e RJ45 plugs

Specifications

OVERVIEW	
Style	Cat5/5e
Model Type	Bulk Cables
Cable Types	CAT5/CAT5E
INPUT	
Cable Length (ft.)	1000
Cable Length (m)	304.80



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

PHYSICAL	
Shipping Weight (lbs.)	26
Shipping Weight (kg)	11.79
Color	Gray
CONNECTIONS	
Connector A	RJ45 (MALE)
Connector B	RJ45 (MALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.