

4U Hinged Wall-Mount Patch Panel Bracket

MODEL NUMBER: **N060-004**



Description

Tripp Lite's heavy duty 14-gauge steel, 4U (7.0") wall mount patch panel bracket, is the ideal alternative to a full size rack. Standard EIA 19-inch width allows installation of any 19inch patch panel. Laser cut metal (not punched) keeps all edges smooth, greatly reducing the possibility of injury, and, wear on cable jackets. Universal mounting for right or left hinging. Keyholes are spaced 16inches for mounting on wall studs. Stamped, horizontal reinforcement ribs allow for greater sturdiness and stability, and allow the addition of a rear cutout for feeding cable through a wall opening. Smooth, glossy black finish.

Features

- 4U height (7.0"), 6inch depth
- Laser cut for smooth edges
- 16 -inch center mounting
- Universal left or right hinge mounting
- Rear cut-out for through the wall cabling
- Standard EIA 19inch width accepts any manufacturers EIA compliant patch panel
- Smooth, black glossy finish
- Heavy duty 14 gauge steel with stamped reinforcement ribs

Highlights

- Laser cut 14-gauge steel results in smooth edges
- Keyholes on 16-inch centers plus through-the-wall cabling cut-out
- Accepts any standard 19inch Patch Panels
- 4U Height (7.0"): 19"wide x 7.0" high x 6.0" deep
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

- 4U Wallmount Patch Panel Bracket
- Pkg 10 mounting screws

Specifications

OVERVIEW	
Model Type	Patch Panel Brackets
Accessories Type	Mounting Bracket
PHYSICAL	
Installed Whole System Maximum Rack Depth (in.)	5.5



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Installed Whole System Maximum Rack Depth (cm)	13.97
Rack Height (U Spaces)	4
Shipping Dimensions (hwd / in.)	6.5 x 20.5 x 7.5
Shipping Dimensions (hwd / cm)	16.51 x 52.07 x 19.05
Shipping Weight (lbs.)	5.7
Shipping Weight (kg)	2.59
Unit Dimensions (hwd / in.)	7 x 19 x 6
Unit Dimensions (hwd / cm)	17.78 x 48.26 x 15.24
Unit Weight (lbs.)	5
Unit Weight (kg)	2.27
Color	Black
Weight Capacity - Stationary (lbs.)	35
Weight Capacity - Stationary (kg)	15.9
CERTIFICATIONS	
NOM (Mexico)	Tested to NOM (Mexico)
Approvals	EIA-310-D, IEC 60297-3-100, DIN 41494, RoHS, UL 60950
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.