

Cat5e 350MHz Molded Shielded Patch Cable (RJ45 M/M) - Gray, 25-ft.

MODEL NUMBER: **N105-025-GY**



Highlights

- Protect your network data from EMI/RFI interference
- Molded boot provides extra strain-relief and durability

Package Includes

- 25ft Gray Cat5e Shielded Patch Cable

Description

Protect your high-speed network from noise and electromagnetic interference with Tripp Lite's 25-ft. gray, Category 5e (Cat5e) Shielded patch cable. This cable features 2 shielded RJ45 gold molded male connectors with integral strain relief. The cable is manufactured from PVC, 4-pair, stranded shielded twisted pair, and is rated for 350MHz/1Gbps communication.

Features

- Provides EMI/RFI shielding in Ethernet networks
- Shielded RJ45 connectors with gold-plated contacts
- 4-pair 24 AWG Stranded STP with drain wire
- Molded boot for extra strain-relief and durability
- TSB 568B (AT&T 258A) Wiring
- TIA/EIA and UL Certified

Specifications

| OVERVIEW | |
|--------------------|------------|
| Style | Cat5/5e |
| Model Type | Shielded |
| Cable Types | CAT5/CAT5E |
| INPUT | |
| Cable Length (ft.) | 25 |
| Cable Length (m) | 7.62 |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| PHYSICAL | |
|-------------------------------------|---------------------------|
| Color | Gray |
| CONNECTIONS | |
| Connector A | RJ45 (MALE) |
| Connector B | RJ45 (MALE) |
| Number of Connectors | 2 |
| CERTIFICATIONS | |
| Certifications | RoHS-Compliant |
| WARRANTY | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.