

Cat5e 350MHz Molded Shielded Patch Cable (RJ45 M/M) - Gray, 100-ft.

MODEL NUMBER: **N105-100-GY**



Highlights

- Protect your network data from EMI/RFI interference
- Molded boot provides extra strain relief and durability

Package Includes

- 100-ft. Cat5e Gray Shielded Patch Cable

Description

Protect your high-speed network from noise and electromagnetic interference with Tripp Lite's 100-ft. Category 5e (Cat5e) Gray Shielded Patch Cable. This cable features 2 shielded RJ45 Gold molded male connectors with integral strain relief. The cable is manufactured from PVC, 4-pair, stranded shielded twisted pair, and is rated for 350MHz/1Gbps communication.

Features

- Provides EMI/RFI shielding in Ethernet networks
- Shielded RJ45 connectors with gold-plated contacts
- 4-pair 24 AWG Stranded STP with drain wire
- Molded boot for extra strain relief and durability
- TSB 568B (AT&T 258A) Wiring
- TIA/EIA and UL Certified

Specifications

OVERVIEW	
Style	Cat5/5e
Model Type	Shielded
Cable Types	CAT5/CAT5E
INPUT	
Cable Length (ft.)	100
Cable Length (m)	30.48



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

PHYSICAL	
Color	Gray
CONNECTIONS	
Connector A	RJ45 (MALE)
Connector B	RJ45 (MALE)
Number of Connectors	2
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.