



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cat6 Gigabit Molded Shielded Patch Cable (RJ45 M/M) - Gray, 25-ft.

MODEL NUMBER: **N125-025-GY**



Highlights

- Protect your network data from EMI/RFI interference
- Molded boot provides extra strain-relief and durability

Package Includes

- 25ft Gray Cat6 Shielded Patch Cable

Description

Protect your high-speed network from noise and electromagnetic interference with Tripp Lite's 25-ft. gray, Category 6 (Cat6) Shielded patch cable. This cable features 2, shielded RJ45 50micron Gold molded male connectors with integral strain relief. The cable is manufactured from PVC, 4-pair, stranded shielded twisted pair, and is rated for 550MHz/1Gbps communication.

Features

- Gigabit rated Cat6 Shielded Patch Cables
- Provides EMI/RFI shielding in Ethernet networks
- 4-pair 26 AWG Stranded STP with drain wire
- Shielded RJ45, w/50-micron gold plated contacts
- Molded boot for extra strain-relief and durability
- TSB 568B (AT&T 258A)Wiring
- TIA/EIA and UL Certified

Specifications

OVERVIEW	
Style	Cat6/6e/6a
Model Type	Shielded
Cable Types	CAT6
INPUT	
Cable Length (ft.)	25



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cable Length (m)	7.62
PHYSICAL	
Color	Gray
CONNECTIONS	
Connector A	RJ45 (MALE)
Connector B	RJ45 (MALE)
Number of Connectors	2
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.