



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cat6 Gigabit Molded Shielded Patch Cable (RJ45 M/M) - Gray, 50-ft.

MODEL NUMBER: **N125-050-GY**



Highlights

- Protect your network data from EMI/RFI interference
- Molded boot provides extra strain-relief and durability

Package Includes

- 50ft Gray Cat6 Shielded Patch Cable

Description

Protect your high-speed network from noise and electromagnetic interference with Tripp Lite's 50-ft. gray, Category 6 (Cat6) Shielded patch cable. This cable features 2, shielded RJ45 50micron Gold molded male connectors with integral strain relief. The cable is manufactured from PVC, 4-pair, stranded shielded twisted pair, and is rated for 550MHz/1Gbps communication.

Features

- Gigabit rated Cat6 Shielded Patch Cables
- Provides EMI/RFI shielding in Ethernet networks
- 4-pair 26 AWG Stranded STP with drain wire
- Shielded RJ45, w/50-micron gold plated contacts
- Molded boot for extra strain-relief and durability
- TSB 568B (AT&T 258A)Wiring
- TIA/EIA and UL Certified

Specifications

| OVERVIEW | |
|--------------------|------------|
| Style | Cat6/6e/6a |
| Model Type | Shielded |
| Cable Types | CAT6 |
| INPUT | |
| Cable Length (ft.) | 50 |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| | |
|-------------------------------------|---------------------------|
| Cable Length (m) | 15.24 |
| PHYSICAL | |
| Color | Gray |
| CONNECTIONS | |
| Connector A | RJ45 (MALE) |
| Connector B | RJ45 (MALE) |
| Number of Connectors | 2 |
| WARRANTY | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.