

## Cat6 Gigabit Snagless Molded Patch Cable (RJ45 M/M) - Green, 20-ft.

MODEL NUMBER: **N201-020-GN**



### Description

With Tripp Lite's new category 6 molded patch cables you can stay ahead of the game by using this high-speed cable to distribute data, voice and video. These cables deliver stable performance up to 550MHz. Each comes UL verified meets EIA/TIA Cat6 TIA/EIA-568-B-2.1 draft 9 standards. Constructed with high-quality copper wire and a staggered-pin plug design, near-end crosstalk levels are kept to a minimum. Designed for use in category 6, category 5e and category 5 applications. Cat6 cables are available in a variety of colors with a snagless boot preventing cable snags.

### Features

Meets category 6 cabling standards

Premium cabling for category 6, category 5e and category 5 applications

Length: 20 ft. / Color: Green / Connectors: RJ45 male

Drastically reduce impedance and structural return loss compared to standard 100MHz wire

High-quality copper wire and a staggered-pin plug design to keep near-end crosstalk levels to a minimum

Feature molded connectors with integral strain relief

Snagless design protects the locking tabs on the RJ45 connectors from being damaged or snapped off during installation

PVC 4-pair stranded UTP

Deliver stable performance up to 550MHz/1 Gbps communication

Meets most current industry standards including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801 and ETL (category 6 draft 11)

Available in other colors and lengths

### Highlights

- Premium cabling for Category 6, Category 5e and Category 5 applications—rated for 550 MHz/1 Gbps communications
- Designed to meet Category 6 specifications; reduces cross-talk and return loss
- IEC 802.3ab
- PVC 4-pair stranded UTP
- All cables feature boots with integral strain-relief and RJ45 (Male) connectors

### Applications

- Cat5e/Cat6 110-style patch panels and jacks
- 66M-type telephone blocks

### System Requirements

- For 1000 Base-T (1Gbps Ethernet), 10/100 Base-T (Ethernet), 100 Mbps TPDDI, 155 Mbps ATM, ISDN, voice and Token Ring TYPE 3 applications as well as EIA/TIA applications.

### Package Includes

- 20-ft. Cat6 Green Gigabit Patch Cord Snagless Molded



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

## Specifications

OVERVIEW	
Style	Cat6/6e/6a
Model Type	Snagless
Cable Types	CAT6
PRODUCT OVERVIEW	
Product Overview	Cat6 Gigabit Green Snagless Patch Cable RJ45 - 20'
INPUT	
Cable Length (ft.)	20
Cable Length (m)	6.10
PHYSICAL	
Color	Green
CONNECTIONS	
Connector A	RJ45 (MALE)
Connector B	RJ45 (MALE)
Number of Connectors	2
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.