

Cat6 Gigabit Molded Flat Patch Cable (RJ45 M/M) - Blue, 25-ft.

MODEL NUMBER: **N201-025-BL-FL**



Description

Tripp Lite's high performance Flat Cat6 gigabit Ethernet patch cables are perfect for connecting your PC to a network in areas where space is tight. With all the reliability and performance of a standard Cat 6 patch cable, this 1.2mm thick cable is ideal for under-carpet, baseboard, etc, applications. Can be used in Cat5e installations as well. Cables comply with EIA/TIA 568 specifications and are UL rated. Flat design reduces NEXT(Near end crosstalk).

Features

- Thin, Flat flexible cable for confined spaces
- Meets Category 6 cabling standards
- High-quality copper wire and a shortened body plug design
- Feature molded connectors with integral strain relief
- EIA/TIA 568 Compliant
- Up to 1Gbps transfer rates

Specifications

OVERVIEW	
Style	Cat6/6e/6a
Model Type	Snagless
Cable Types	CAT6
INPUT	
Cable Length (ft.)	25

Highlights

- Thin, Flat flexible cable for confined spaces
- Meets Category 6 cabling standards
- High-quality copper wire and a shortened body plug design
- Feature molded connectors with integral strain relief

System Requirements

- For 1000 Base-T (1Gbps Ethernet), 10/100 Base-T (Ethernet), 100 Mbps TPDDI, 155 Mbps ATM, ISDN, voice and Token Ring TYPE 3 applications as well as EIA/TIA applications.

Package Includes

- 25ft Blue Flat Cat6 Molded Patch Cable



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cable Length (m)	7.62
PHYSICAL	
Color	Blue
CONNECTIONS	
Connector B	RJ45 (MALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.