

## Cat6 Gigabit Snagless Molded Patch Cable (RJ45 M/M) - Green, 25-ft.

MODEL NUMBER: **N201-025-GN**



### Description

With Tripp Lite's new category 6 molded patch cables you can stay ahead of the game by using this high-speed cable to distribute data, voice and video. These cables deliver stable performance up to 550MHz. Each comes UL verified meets EIA/TIA Cat6 TIA/EIA-568-B-2.1 draft 9 standards. Constructed with high-quality copper wire and a staggered-pin plug design, near-end crosstalk levels are kept to a minimum. Designed for use in category 6, category 5e and category 5 applications. Cat6 cables are available in a variety of colors with a snagless boot preventing cable snags.

### Features

- Meets category 6 cabling standards
- Premium cabling for category 6, category 5e and category 5 applications
- Length: 25-ft. Color: green. Connectors: RJ45 male.
- Drastically reduce impedance and structural return loss compared to standard 100MHz wire
- High-quality copper wire and a staggered-pin plug design to keep near-end crosstalk levels to a minimum
- Feature molded connectors with integral strain relief
- Snagless design protects the locking tabs on the RJ45 connectors from being damaged or snapped off during installation
- PVC 4-pair stranded UTP
- Deliver stable performance up to 550MHz/1 Gbps communication
- Meets most current industry standards including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801 and ETL (category 6 draft 11)
- Available in other colors and lengths

### Highlights

- Meets Category 6 cabling standards
- Drastically reduce impedance and structural return loss compared to standard 100Mhz wire
- High-quality copper wire and a shortened body plug design
- Feature molded connectors with integral strain relief
- Snagless boots protect the locking tabs on the RJ45 connectors from being damaged during installation

### System Requirements

- For 1000 Base-T (1Gbps Ethernet), 10/100 Base-T (Ethernet), 100 Mbps TPDDI, 155 Mbps ATM, ISDN, voice and Token Ring TYPE 3 applications as well as EIA/TIA applications

### Package Includes

- 25-ft. Cat6 Green Gigabit Patch Cord Snagless Molded

## Specifications

### OVERVIEW



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Style	Cat6/6e/6a
Model Type	Snagless
Cable Types	CAT6
<b>INPUT</b>	
Cable Length (ft.)	25
Cable Length (m)	7.62
<b>PHYSICAL</b>	
Color	Green
<b>CONNECTIONS</b>	
Connector A	RJ45 (MALE)
Connector B	RJ45 (MALE)
<b>CERTIFICATIONS</b>	
Certifications	RoHS-Compliant
Approvals	EIA/TIA Cat6 TIA/EIA- 568-B-2.1, draft 9 standards
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.