

Cat6 Gigabit Molded Patch Cable (RJ45 Left Angle M to RJ45 M) - Blue, 3-ft.

MODEL NUMBER: **N204-003-BL-LA**



Highlights

- Space saving design
- Left Angle connector to Straight
- Cat6 Gigabit rated

System Requirements

- Use with Cat6, Cat5e, Cat5, or VoIP networks

Package Includes

3ft Blue Cat6 Left Angle to Straight RJ45 - RJ45 Patch cable

Description

Tripp Lite's Angled Cat6 Patch Cables are ideal for where connections are in tight quarters. Choose from Up, Down, Left, and Right angled cables, depending on your situation. Reduces stress on the cable, and excessive bending. Great for switches and patch panels in networking racks, or behind desks and wall connections. Meets or exceeds Cat6 specifications. Fully molded ends for a lifetime of use.

Features

- 3ft Blue Cat6, Left Angle to Straight RJ45 - RJ45 Patch cable
- PVC 4 Pair Stranded Conductors, 24AWG
- Fully Molded Ends
- ETL Verified to TIA/EIA -568-B
- 550Mhz Gigabit Speed Rated

Specifications

OVERVIEW	
Style	Cat6/6e/6a
Model Type	Angled
Cable Types	CAT6
INPUT	
Cable Length (ft.)	3
Cable Length (m)	0.91
PHYSICAL	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Color	Blue
CONNECTIONS	
Connector A	RJ45 (MALE)
Connector B	RJ45 (MALE) - LEFT ANGLE
CERTIFICATIONS	
Certifications	Tested to
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.