

## Cat6 Gigabit Bulk Solid Plenum-Rated PVC Cable - Gray, 1000-ft.

MODEL NUMBER: **N224-01K-GY**



### Description

With Tripp Lite's Category 6 Plenum Rated Bulk cable, you can stay ahead of the game by using this high-speed cabling to distribute data, voice and video. This Plenum rated cable is designed for premise (in-wall) cabling applications in air ducts and drop ceilings. Constructed with high-quality copper wire, near-end crosstalk levels are kept to a minimum. This 1,000ft. spool of bulk solid plenum cable makes industrial runs a snap for the do-it-yourself cable guy. General Cat6 patch cables are available in a variety of colors and sizes.

### Features

- Designed for premise (in-wall) cabling applications in air ducts and drop ceilings
- Premium cabling for category 6, category 5e and category 5 applications
- Color: Gray / Length: 1000-ft.
- 24 AWG 4-pair solid cable with Gray Plenum ( CMP ) jacket
- Deliver stable performance up to 550MHz/ 1 Gbps communication
- Meets most current industry standards including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801 and ETL (category 6 draft 11)
- Available in PVC cable as well (N222-01K-GY and N222-01K-BL)
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

### Highlights

- Premium cabling for Category 6, Category 5e and Category 5 applications-rated for 350 MHz/1 Gbps communications
- Designed to meet Category 6 specifications: reduces cross-talk and return loss
- IEC 802.3ab
- 1,000ft Box PLENUM ( CMP ) 4-pair Solid UTP
- Designed for premise (in-wall) cabling applications in air ducts and drop ceilings
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

### System Requirements

- For 1000 Base-T (1Gbps Ethernet), 10/100 Base-T (Ethernet), 100 Mbps TPDDI, 155 Mbps ATM, ISDN, voice and Token Ring TYPE 3 applications as well as EIA/TIA applications.

### Package Includes

- 1000-ft. Cat6 Gigabit Bulk 4PR Solid Plenum Cable

## Specifications

OVERVIEW	
Style	Bulk Spooled PVC
Model Type	Bulk Cables
Cable Types	CAT6



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

INPUT	
Cable Length (ft.)	1000
Cable Length (m)	304.80
PHYSICAL	
Color	Gray
CERTIFICATIONS	
Approvals	EIA/TIA CAT6 TIA/EIA- 568-B-2.1, DRAFT 9 standards
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.