

16-Port Fiber Patch Panel, 1U (LC/LC)

MODEL NUMBER: **N490-016-LCLC**



Highlights

- Simplified Fiber Optic Patching
- Multimode 62.5/125 or 50/125
- 16 ports in 1U of rackspace

Package Includes

- 16 Port LC/LC Duplex Fiber Optic Patch Panel

Description

Tripp Lite's 16-Port 1U Rackmount LC/LC Fiber Optic Patch Panel provides efficient and easy management of fiber optic cables in the rack or cabinet. Pre-loaded, feed-thru duplex multimode connectors are mounted on a 16-gauge, cold rolled, black powder coated steel panel. Use with 62.5/125 or 50/125 multimode fiber patch cables. Panel measures 19" wide by 1.75" high.

Features

- 16 ports LC/LC
- Only 1U of rack-space
- Use with 62.5/125 or 50/125 fiber patch cables
- Available in ST/ST, ST/SC, SC/SC, LC/LC, MTRJ/MTRJ

Specifications

OVERVIEW	
Model Type	Patch Panels
CONNECTIONS	
Connector A	LC (FEMALE) (X16)
Connector B	LC (FEMALE) (X16)
Number of Connectors	16
Ports	16
WARRANTY	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Product Warranty Period (Worldwide)	Lifetime limited warranty
-------------------------------------	---------------------------

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.