

# Duplex Multimode 62.5/125 LSZH Fiber Optic Cable, 1000-ft. Bulk

MODEL NUMBER: N549-01K



### **Highlights**

- Bulk 62.5/125 Multimode Duplex
   Fiber Optic Cable
- Low-Smoke, Zero Halogen (LSZH) jacket
- · Zip-Cord Style

### Package Includes

Carton of 1,000ft Duplex 62.5/125 Multimode cable

### Description

Tripp Lite N549-01K bulk 62.5/125 multimode fiber optic cable is ideal for long backbone runs, or for making your own Fiber patch cables. Individual fibers surrounded by Kevlar yarn for maximun tensile strength and protection. Low-Smoke, Zero Halogen (LSZH) jacket.

#### **Features**

- Bulk 62.5/125 Multimode Duplex Fiber Optic Cable
- Low-Smoke, Zero Halogen jacket
- Zip-Cord Style
- Cable marked every meter
- Temp Range: -20C to +70C
- Suitable for Indoor Use
- 7lb Reel

## **Specifications**

OVERVIEW	
Clad Diameter	125mu
Core Diameter	62.5mu
Number of Fibers	2
Shipping Weight	7lb
Network Speed	1Gbps
Style	Fiber Optic
Fiber Type	62.5/125 - OM1



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Model Type	Bulk Cables	
INPUT		
Cable Length (ft.)	1000	
Cable Length (m)	304.8	
ENVIRONMENTAL		
Operating Temperature Range	-20C to +70C	
WARRANTY		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.