

OM3 can support 40GBASE-SR4 / 100GBASE-SR10 in applicable parallel optics networks

MTP/MPO Fan-Out Cable, MTP/MPO to 8xLC, 40GbE, 40GBASE-SR4, OM3 Plenum-Rated - Aqua, 3M (10-ft.)

MODEL NUMBER: **N844-03M-8LC-P**



Highlights

- MTP / MPO to 8 x LC Fan-out Cable
- OM3, 40GbE rated, 40GBASE-SR4
- 50/125 Multimode

Applications

- Used with 40GBASE-SR4 networking hardware

Package Includes

3M (10-ft.) MTP / MPO Fan-out Cable, MTP/MPO to 8 x LC, 40GbE OM3 Plenum

Description

Tripp Lite's MPO/MTP Multi-Fiber cabling system is ideally suited for a high density environment that demands space saving and reduced cable management solutions. MPO/MTP fan-outs support various connections from multi-fiber to single-fiber out. N844-xxM-8LC-P cables utilize 8 fibers to fully transmit 40GBASE-SR, 4 fibers in each direction transmitting 10Gb each.

Features

- MTP / MPO to 8 x LC, 3 Meter Fan-out Cable
- 40GbE rated OM3 50/125 Multimode
- Plenum rated jacket

Specifications

OVERVIEW	
Network Speed	10Gbps / 40Gbps / 100Gbps
Style	50/125 Multimode Fiber
Fiber Type	50/125 - OM3
Model Type	MTP/MTP
Cable Types	FIBER OPTIC
INPUT	
Cable Length (ft.)	10



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cable Length (m)	3
PHYSICAL	
Color	Aqua
CONNECTIONS	
Connector A	MTP
Connector B	LC (X8)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.