

Universal AC Power Adapter Cord, 10A, 18AWG (IEC-320-C14 to NEMA 5-15R), 2-ft.

MODEL NUMBER: P002-002-10A



Highlights

- 2-ft. C14 to 5-15R power cord
- Allows you to plug a power cord with a NEMA 5-15P plug into the IEC-320-C13 outlet of a PDU or UPS.
- Frees up a wall outlet
- 18AWG, SJT, 10A, 125V
- UL Listed

Package Includes

- 2-ft. AC Power Adapter Cord - PC Style (IEC-320-C14) plug to AC Style (NEMA 5-15R) receptacle

Description

Tripp Lite makes your PC installation one step easier. This 2-ft. AC Power Adapter Cord allows you to plug a power cord with a NEMA 5-15P plug into the IEC-320-C13 outlet of a PDU or UPS. Features a NEMA 5-15R receptacle with an IEC-320-C14 plug. UL listed.

Features

- 2-ft. C14 to 5-15R power cord
- Allows you to plug a power cord with a NEMA 5-15P plug into the IEC-320-C13 outlet of a PDU or UPS.
- Frees up a wall outlet
- 18AWG SJT, 10A, 125V
- UL listed

Specifications

OVERVIEW	
Style	Power Cables
Model Type	Power Cords
Cable Types	POWER
INPUT	
Cable Length (ft.)	2
Cable Length (m)	0.61
PHYSICAL	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Color	Black
CONNECTIONS	
Connector B	NEMA 5-15R
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.