

Standard Computer Power Extension Cord, 10A, 18AWG (IEC-320-C14 to IEC-320-C13), 15-ft.

MODEL NUMBER: P004-015



Highlights

- UL Listed
- C13 - C14
- 18AWG SJT, 10A, 100-250V

Package Includes

- 15-ft. Universal AC Power Cord - PC Style Male (IEC-320-C14) to PC Style Female (IEC-320-C13)

Description

Tripp Lite's line of AC power cords offer PC users a solution to their power connectivity problems. This handy 15ft. cord can be used to extend the power cord on any PC or device with a C14 plug; or, to connect your C14 PC or device directly to the C13 port on your PDU or UPS. Features an IEC-320-C14 to IEC-320-C13 connection. UL listed.

Features

- UL Listed
- 15-ft. power extension cord for your PC or device with a C14 plug
- Directly connect a C14 PC or device to the C13 port on your PDU or UPS
- Plug type: IEC-320-C14 (male) to IEC-320-C13 (female)
- 18AWG SJT, 10A, 100-250V

Specifications

OVERVIEW	
Style	Power Cables
Model Type	Power Cords
Cable Types	POWER
INPUT	
Cable Length (ft.)	15
Cable Length (m)	4.57



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

PHYSICAL	
Color	Black
CONNECTIONS	
Connector A	IEC-320-C14
Connector B	IEC-320-C13
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.