



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Heavy-Duty Computer Power Cord, 14AWG 15A (NEMA 5-15P to IEC-320-C13), 2-ft.

MODEL NUMBER: **P007-002**



Highlights

- C13 to 5-15P Power Cable, 2 ft.
- 14 AWG x 3C - 15A - 125V
- RoHS Compliant
- UL Listed

Package Includes

C13 to 5-15P Power Cable, 2 ft.

Description

Use Tripp Lite's P007-002 in server applications that require a higher rated, heavier gauge cable. C13 to 5-15P connectors, 3 x 14 AWG conductors, 15A / 125V rating.

Features

- Molded, Heavy-Duty Power Cable, 2 ft.
- IEC-60320-C13 to NEMA 5-15P
- 14 AWG x 3C, SJT, 15A, 125 Volt
- RoHS Compliant
- UL Listed

Specifications

OVERVIEW	
Style	Power Cables
Model Type	Power Cords
Cable Types	POWER
INPUT	
Cable Length (ft.)	2
Cable Length (m)	0.61
PHYSICAL	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Color	Black
CONNECTIONS	
Connector A	NEMA 5-15P
Connector B	IEC-320-C13
Number of Connectors	2
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.