

Heavy-Duty Computer Power Cord, 15A, 14AWG (IEC-320-C13 to NEMA L6-20P), 6-ft.

MODEL NUMBER: **P011-006**



Highlights

- C13 to L6-20P Power Cable, 6ft.
- 14 AWG x 3C, 250V
- RoHS Compliant
- UL Listed

Package Includes

- C13 to L6-20P Power Cable, 6ft

Description

Use Tripp Lite's P011-006 in server applications that require a higher rated, heavier gauge cable. C13 to L6-20P connectors, 3 x 14 AWG conductors, 15A/250V rating.

Features

- Molded, Heavy-Duty Power Cable, 6 ft.
- IEC-60320-C13 to NEMA L6-20P
- 14 AWG x 3C, SJT, 15A, 250 Volt
- RoHS Compliant
- UL Listed

Specifications

OVERVIEW	
Style	Power Cables
Model Type	Power Cords
Cable Types	POWER
PRODUCT OVERVIEW	
Product Overview	Heavy-Duty C13 to L6-20P Power Cable
INPUT	
Cable Length (ft.)	6



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cable Length (m)	1.83
PHYSICAL	
Color	Black
CONNECTIONS	
Connector A	NEMA L6-20P
Connector B	IEC-320-C13
Number of Connectors	2
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.