

## Heavy-Duty Power Cord, 15A,14AWG (NEMA 5-15P to IEC-320-C15), 8-ft.

MODEL NUMBER: **P019-008**



### Description

Tripp Lite's 5-15P -to- C15 power cords allow connection from high voltage network hardware utilizing C15 type connectors electrical outlets with 5-15R type inputs. Heavy-duty 14AWG wire supports voltages up to 250V. Molded ends ensure a lifetime of use.

### Features

- Heavy-duty power cord supports up to 250V
- 100~250V, 15A, 14AWG, SJT
- Flexible 14AWG wire for easy routing
- Use with Cisco, HP and other hardware that uses C15 type power connections
- UL Listed

## Specifications

OVERVIEW	
Style	Power Cable
Model Type	Power Cords
Cable Types	POWER
INPUT	
Cable Length (ft.)	8
Cable Length (m)	2.44
PHYSICAL	

### Highlights

- 8-ft. heavy-duty power cord, 5-15P-to-C15
- 100~250V, 15A, 14AWG, SJT
- UL Listed

### Applications

- Ideal for connecting network hardware with C15 power connections to 5-15R power outlets
- Equivalent to HP 8120-5337
- Equivalent to Cisco CAB-C15-AC=

### Package Includes

- 8-ft. Heavy Duty 14AWG Power Cord, 5-15P to C15



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Color	Black
<b>CONNECTIONS</b>	
Connector A	NEMA 5-15P
Connector B	IEC-320-C15
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.