



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Heavy-Duty Power Splitter Y Cable, 15A, 14AWG (IEC-320-C20 to 2x IEC-320-C13), 2-ft.

MODEL NUMBER: **P032-002-2C13**



Highlights

- Connect two devices to one power outlet
- Plug type - C20 to 2 x C13
- 14AWG (2.08mm²), SJTW, 15A, 100-250V

Package Includes

- 2-ft. AC Power Splitter Cable, C20 to 2 x C13

Description

Tripp Lites P032-002-2C13, 2ft Universal AC Power Cord Splitter, allows you to connect two devices with C14 connections, such as servers, to one power outlet. Cuts down on cabling, as well as frees up space on UPS's, Surge Protectors, PDU's etc. Heavy gauge 14AWG (2.08mm²) wire handles 15Amps, and 100-250 Voltage range.

Features

- Power two computers or other device from one outlet
- Plug type - C20 to 2 x C13
- 14AWG (2.08mm²), SJTW, 15A, 100-250V

Specifications

OVERVIEW	
Style	Power Cables
Model Type	Power Cords
Cable Types	POWER
INPUT	
Cable Length (ft.)	2
Cable Length (m)	0.61
PHYSICAL	
Color	Black



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

CONNECTIONS	
Connector A	IEC-320-C20
Connector B	IEC-320-C13 (X2)
Number of Connectors	3
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.