



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Heavy-Duty Power Extension Cord, 20A, 12AWG (IEC-320-C19 to IEC-320-C20), 6-pack, 2-ft.

MODEL NUMBER: **P036-002-6**



Highlights

- C19 to C20 Power Cord, 2 ft., 6-Pack
- 12AWG x 3C, 20 Amp Rated
- RoHS Approved

Package Includes

- (x6) C19 to C20 Power Cords, 2 ft.

Description

Clean up your racks and cabinets with Tripp Lite's P036-002-6 6-pack of 2 ft., C19 to C20 heavy duty power cords. Constructed of 12AWG wire, these cables are 20-Amp rated, 250V - ideal for use with Blade Server Chassis.

Features

- Molded, Heavy-Duty Power Cord, 2 ft., 6-Pack
- IEC-60320-C19 to IEC-60320-C20
- 12AWG x 3C, SJTW, 20A, 250Volt
- RoHS Approved

Specifications

OVERVIEW	
Style	Power Cables
Model Type	Power Cords
Cable Types	POWER
INPUT	
Cable Length (ft.)	2
Cable Length (m)	0.61
PHYSICAL	
Color	Black



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

CONNECTIONS	
Connector A	IEC-320-C20
Connector B	IEC-320-C19
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.