

## Heavy-Duty Power Extension Y Splitter Cord, 20A, 12AWG (2x IEC-320-C19 to IEC-320-C20), 6-ft.

MODEL NUMBER: **P036-006-2C19**



### Highlights

- Connect two devices to one power outlet
- Plug type - C20 to 2 x C19
- 12AWG (3.31mm<sup>2</sup>), SJTW, 20A, 100-250V

### Package Includes

- 6-ft. AC Splitter Power Cord, C20 to 2 x C19

### Description

Tripp Lite's P036-006-2C19, 6ft Universal AC Splitter Power Cord, allows you to connect two devices with C20 connections, such as blade server chassis, to one power outlet. Cuts down on cabling, as well as frees up space on UPS systems, Surge Protectors, PDUs, etc. Main trunk cable measures 47" from C20 plug to the splitter housing, 3" housing, and 22" each on the two C19 legs.

### Features

- Power two computers or other device from one outlet
- Plug type - C20 to 2 x C19
- 12AWG (3.31mm<sup>2</sup>), SJTW, 20A, 100-250V
- 6ft overall length - 47" from C20 to split, 22" from split to C19's

## Specifications

OVERVIEW	
Style	Power Cables
Model Type	Power Cords
Cable Types	POWER
INPUT	
Cable Length (ft.)	6
Cable Length (m)	1.83
PHYSICAL	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Color	Black
<b>CONNECTIONS</b>	
Connector A	IEC-320-C20
Connector B	IEC-320-C19 (X2)
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.