

Heavy-Duty Power Extension Cord, 20A, 12AWG (IEC-320-C19 to IEC-320-C20) 10-ft.

MODEL NUMBER: **P036-010**



Highlights

- C19 to C20 Power Cord, 10 ft.
- 12AWG x 3C, 20 Amp Rated
- RoHS Approved

Package Includes

- C19 to C20 Power Cord, 10 ft.

Description

Use Tripp Lite's P036-010 in server applications that require a higher rated, heavier gauge cable. C19 to C20 connectors, 3 x 12ga conductors, 20AMP rated, 250V - ideal for use with Blade Server Chassis.

Features

- Molded, Heavy-Duty Power Cord, 10 ft.
- IEC-60320-C19 to IEC-60320-C20
- 12AWG x 3C, SJTW, 20A, 250Volt
- RoHS Approved

Specifications

OVERVIEW	
Style	Power Cables
Model Type	Power Cords
Cable Types	POWER
INPUT	
Cable Length (ft.)	10
Cable Length (m)	3.05
PHYSICAL	
Color	Black



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

CONNECTIONS	
Connector A	IEC-320-C20
Connector B	IEC-320-C19
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.