



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Heavy-Duty Y Splitter Power Cord for PDU and UPS, 20A, 10AWG (NEMA L6-20P to 2x NEMA L6-20R), 1 ft.

MODEL NUMBER: **P039-001-2**



Highlights

- L6-20P to 2 x L6-20R Power Splitter
- 10AWG x 3C, 20-Amp, 250V
- RoHS Compliant

Package Includes

1-ft. L6-20P to 2 x L6-20R Power Splitter Cord

Description

Tripp Lite's Power Splitter Cord - L6-20P male to 2 x L6-20R female. Constructed with 3 x 10ga copper conductors, fully molded ends and 250V/20A rating.

Features

- Molded, Heavy-Duty Power Splitter Cord, 1ft.
- NEMA L6-20P to 2 x NEMA L6-20R
- 10AWG x 3C, SJT, 20A, 250Volt
- RoHS Compliant

Specifications

OVERVIEW	
Style	Power Cables
Model Type	Power Cords
Cable Types	POWER
INPUT	
Cable Length (ft.)	1
Cable Length (m)	0.30
PHYSICAL	
Color	Black



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

CONNECTIONS	
Connector A	NEMA L6-20P
Connector B	NEMA L6-20R (X2)
Number of Connectors	3
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.