

Heavy-Duty Power Extension Cord, 20A, 12AWG (IEC-320-C19 to NEMA L6-20P), 6-ft.

MODEL NUMBER: P040-006



Highlights

- C19 to L6-20P power cord, 6 ft.
- 12AWG, SJT, 20A, 250V
- RoHS compliant

Package Includes

- 6 ft. C19 to L6-20P Power Cord

Description

Tripp Lite's Heavy Duty C19 to L6-20P 6 ft. power cord is constructed with 3 x 12AWG copper conductors, fully molded ends, and 250V/20A rating.

Features

- Molded, Heavy-Duty Power Cord, 6 ft.
- IEC-320-C19 to NEMA L6-20P
- 12AWG, SJT, 20A, 250V
- RoHS compliant

Specifications

OVERVIEW	
Style	Power cables
Model Type	Power Cords
Cable Types	POWER
INPUT	
Cable Length (ft.)	6
Cable Length (m)	1.8
PHYSICAL	
Color	Black



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

CONNECTIONS	
Connector A	NEMA L6-20P
Connector B	IEC-320-C19
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.