



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Standard Power Extension Cord, 10A, 18AWG (IEC-320-C19 to IEC-320-C14), 6-ft.

MODEL NUMBER: P047-006-10A



Highlights

- C19 to C14 Power Cable, 6 ft.
- 16 AWG x 3C - 10A - 100-250V
- RoHS Compliant

Package Includes

- C19 to C14 Power Cable, 6 ft.

Description

Tripp Lite's C19 to C14 6 ft. power cord is constructed with 3 x 16 AWG copper conductors, fully molded ends, 100-250V / 10A rating.

Features

- Molded Power Cord, 6 ft.
- IEC-60320-C19 to IEC-60320-C14
- 16 AWG x 3C, SJT, 10A, 100-250 Volt
- RoHS Compliant

Specifications

OVERVIEW	
Style	Power Cables
Model Type	Power Cords
Cable Types	POWER
INPUT	
Cable Length (ft.)	6
Cable Length (m)	1.83
PHYSICAL	
Color	Black



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

CONNECTIONS	
Connector A	IEC-320-C14
Connector B	IEC-320-C19
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.